


# Interscale Flexible Rail System for Mounting PCBs



Interscale flexible rail system for mounting PCBs in Interscale SFF Cases. Supports individual mounting of PCBs in combination with a mounting plate.

## FEATURES

Board support is bolted onto mounting plate

PCB (board thickness 1.4 ... 2.6 mm) can be positioned flexibly

## SPECIFICATIONS

|                        |                         |
|------------------------|-------------------------|
| <b>Material:</b>       | Aluminum                |
| <b>Finish:</b>         | Anodized                |
| <b>Product Family:</b> | Interscale              |
| <b>Product Type:</b>   | Mounting Kit            |
| <b>Type:</b>           | Mounting Kit            |
| <b>Works With:</b>     | Small Form Factor Cases |

Table 1/1

| Catalog Number | Length   | Package Quantity | Quick Ship |
|----------------|----------|------------------|------------|
| 24827-023      | 128.55mm | 2                | No         |
| 24827-024      | 173mm    | 2                | No         |
| 24827-025      | 217.45mm | 2                | No         |
| 24827-027      | 306.35mm | 2                | No         |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**