

# Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

## FEATURES

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

## SPECIFICATIONS

**Product Type:** Cabinet  
**Cladding Color Code:** RAL 7021  
**Frame Material:** Steel

Table 1/3

| Catalog Number | Rack Height | Height | Frame Color | Width | Frame Color Code | Cladding Material |
|----------------|-------------|--------|-------------|-------|------------------|-------------------|
| 10630-036      | 42U         | 2000mm | Black Grey  | 600mm | RAL 7021         | Steel             |
| 10630-035      | 42U         | 2000mm | Black Grey  | 600mm | RAL 7021         | Steel             |

| CatalogNumber | Rack Height | Height | Frame Color | Width | Frame Color Code | Cladding Material |
|---------------|-------------|--------|-------------|-------|------------------|-------------------|
| 10630-033     | 38U         | 1800mm | Black Grey  | 600mm | RAL 7021         | Steel             |
| 10630-034     | 38U         | 1800mm | Black Grey  | 600mm | RAL 7021         | Steel             |

Table 2/3

| Catalog Number | Depth | Cladding Color | Package Quantity | Complies With   | Finish        | Material |
|----------------|-------|----------------|------------------|-----------------|---------------|----------|
| 10630-036      | 800mm | Black Grey     | 1                | IEC 60297-3-100 | Powder Coated | Steel    |
| 10630-035      | 600mm | Black Grey     | 1                | IEC 60297-3-100 | Powder Coated | Steel    |
| 10630-033      | 600mm | Black Grey     | 1                | IEC 60297-3-100 | Powder Coated | Steel    |
| 10630-034      | 800mm | Black Grey     | 1                | IEC 60297-3-100 | Powder Coated | Steel    |

Table 3/3

| Catalog Number | Static Load | Quick Ship |
|----------------|-------------|------------|
| 10630-036      | 400kg       | No         |
| 10630-035      | 400kg       | No         |
| 10630-033      | 400kg       | No         |
| 10630-034      | 400kg       | No         |

## ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**