


VMEbus J1/J2 Backplane



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

CERTIFICATIONS



FEATURES

In accordance with ANSI/VITA 1-1994 VME64 standard

Monolithic backplane, 6 U with J1 and J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination active/passive, switchable via jumpers; passive termination preset

Electronic automatic daisy chain (EDC)

Supply voltages provided via power bugs (ring tag M4) or FASTON

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-063	Backplane	3	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-064	Backplane	4	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP

CatalogNumber	Product Type	Number ofSlots	Rack Height	BackplaneType	System Slot	Slot Width
23001-065	Backplane	5	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-066	Backplane	6	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-067	Backplane	7	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-068	Backplane	8	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-080	Backplane	20	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-081	Backplane	21	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-069	Backplane	9	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-070	Backplane	10	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP
23001-072	Backplane	12	6U	VMEbus, J1/J2, with EDC	Slot 1 Left	4HP

Table 2/3

Catalog Number	Connector Type	Power Connector Type	Utility Connector Type	Height	Width	Package Quantity
23001-063	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	59.5mm	1
23001-064	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	79.8mm	1
23001-065	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	100.2mm	1
23001-066	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	120.5mm	1
23001-067	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	140.8mm	1
23001-068	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	161.1mm	1

CatalogNumber	ConnectorType	Power ConnectorType	Utility ConnectorType	Height	Width	Package Quantity
23001-080	DIN 41612, C96	Power Bugs for M4 Cable Lugs	SMCQ, 12-pin, 5-pin Header	263.4mm	405mm	1
23001-081	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	425.3mm	1
23001-069	DIN 41612, C96	Power Bugs for M4 Cable Lugs	SMCQ, 12-pin, 5-pin Header	263.4mm	181.4mm	1
23001-070	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	201.8mm	1
23001-072	DIN 41612, C96	Power Bugs for M4 Cable Lugs	MicroMatch, 8-pin, 5-pin Header	263.4mm	242.4mm	1

Table 3/3	
Catalog Number	Quick Ship
23001-063	No
23001-064	No
23001-065	No
23001-066	No
23001-067	No
23001-068	No
23001-080	No
23001-081	No
23001-069	No
23001-070	No
23001-072	No

ADDITIONAL PRODUCT DETAILS

Other configurations available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE