

Varistar CP Steel Door, Plain With 1-Point Locking



Varistar CP Steel Door, IP 20 with Single Point Locking.

FEATURES

Steel door with single point locking for IP 20 protection class

Opening angle 180°

SPECIFICATIONS

Product Type: Cabinet Door

Protection Rating: IP20

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-493	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-400	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-494	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-401	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-495	29U	1400mm	600mm	Single Point Locking	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-402	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-496	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-403	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-497	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-404	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-498	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-405	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-499	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-406	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-500	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-407	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-501	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-002	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-502	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-009	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-503	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-003	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-504	47U	2200mm	800mm	Single Point Locking	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-010	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-004	52U	2450mm	600mm	Single Point Locking	1	Black Grey
21630-011	52U	2450mm	800mm	Single Point Locking	1	Black Grey

Table 2/2						
Catalog Number	Color Code	Complies With	Finish	Type	Works With	Quick Ship
21630-493	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-400	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-494	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-401	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-495	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-402	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-496	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-403	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-497	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-404	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-498	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-405	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-499	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No

CatalogNumber	Color Code	Complies With	Finish	Type	Works With	Quick Ship
21630-406	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-500	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-407	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-501	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-002	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-502	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-009	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-503	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-003	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-504	RAL 7021	IEC 61587-1	Powder Coated	Steel Door	Varistar CP	No
21630-010	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-004	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No
21630-011	RAL 7021	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE