

Varistar CP Bottom Rear Panel, Shortened



Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPECIFICATIONS

Product Type: Cabinet Door

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-354	38U	1800mm	600mm	IP55	1	Black Grey
21630-356	42U	2000mm	600mm	IP55	1	Black Grey
21630-358	47U	2200mm	600mm	IP55	1	Black Grey
21630-355	38U	1800mm	800mm	IP55	1	Black Grey
21630-357	42U	2000mm	800mm	IP55	1	Black Grey
21630-359	47U	2200mm	800mm	IP55	1	Black Grey

Table 2/2

Catalog Number	Color Code	Finish	Quick Ship
21630-354	RAL 7021	Powder Coated	No
21630-356	RAL 7021	Powder Coated	No
21630-358	RAL 7021	Powder Coated	No
21630-355	RAL 7021	Powder Coated	No
21630-357	RAL 7021	Powder Coated	No
21630-359	RAL 7021	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

The height of the rear panel is 400 mm less than the cabinet height to accommodate the connecting plate.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE