

19" Cable Ducting



19" unit for easy and effective cable management (cable ducting).

CERTIFICATIONS



FEATURES

19" Front panel for cable ducting

SPECIFICATIONS

Accessory Type: Front panel
Product Type: Front Panel
Material: Steel

Table 1/3

Catalog Number	Rack Height	Mounting	Package Quantity	Front Finish	Rear Finish	Color Code
20118-734	1U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-767	1U	Screw-on Front	1	Painted	Painted	RAL 7021
20118-768	2U	Screw-on Front	1	Anodized	Conductive	RAL 7021

CatalogNumber	Rack Height	Mounting	Package Quantity	Front Finish	Rear Finish	Color Code
20118-736	2U	Screw-on Front	1	Painted	Painted	RAL 7035

Table 2/3

Catalog Number	Depth	EMC Shielding	Finish	Height	Rack Width	Type
20118-734	1.5mm	No	Powder Coated	43.6mm	95HP	19" Front Panel
20118-767	1.5mm	No	Powder Coated	43.6mm	95HP	19" Front Panel
20118-768	1.5mm	No	Powder Coated	88.1mm	95HP	19" Front Panel
20118-736	1.5mm	No	Powder Coated	88.1mm	95HP	19" Front Panel

Table 3/3

Catalog Number	Width	Quick Ship
20118-734	483mm	No
20118-767	483mm	No
20118-768	483mm	No
20118-736	483mm	No

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE