


# Minipac Rectangular Shape Case, Wall Mount

## CATALOG NUMBER

**24814-025**



The rectangular Alu-profile case enables a user to insert 4 standard PCBs (height 100 mm x depth 160 mm). The PCBs will be inserted in grooves in the Alu-profile tube. Both sides are covered with 2.5 mm thick L-shaped front panels for wall mounting.

## CERTIFICATIONS



## FEATURES

Accommodates 4 standardized PCBs (height 100 mm, depth 160 mm) or rotated by 90° to accommodate 8 non-standardized PCBs (height 60 mm, depth 160 mm)

PCB thickness 1.6 mm, spacing 10.16 mm (2 HP)

Length D = 160 mm, long side 110.9 mm, short side 70.3 mm

Wall mount assembly

## PRODUCT ATTRIBUTES

Product Type: Small Form Factor Case

Product Family: Minipac

Type: Wall Mount

Height: 112.3mm

Width: 76.2mm

Depth: 160.5mm

Material: Aluminum

Finish: Anodized

Protection Rating: IP40

Cooling: Non-Perforated

Shape: Rectangular

Package Quantity: 1

Length: 160.5mm

## ADDITIONAL PRODUCT DETAILS

Other dimensions on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**