


EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding

Power Utilities



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS



FEATURES

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel

CatalogNumber	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Stainless Steel
24553-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Stainless Steel
24553-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel
24553-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Stainless Steel
24553-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Stainless Steel

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24553-434	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-433	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-432	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-134	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-133	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-132	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Catalog Number	Static Load
24553-434	11 kgf
24553-433	11 kgf
24553-432	11 kgf
24553-134	11 kgf

Catalog Number	Static Load
24553-133	11 kgf
24553-132	11 kgf

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE