

# Varistar ETSI Panel/Slide Mount



Varistar ETSI 23" rack for housing telephone (primarily), computer, audio, and other equipments. It is compatible with the Slim-Line Frame.

## CERTIFICATIONS



## FEATURES

Suitable for Slim-Line frame only

Finish AlZn

St, 2 mm

SPECIFICATIONS

Product Type: Slide Mount  
Material: Steel

| Table 1/1      |        |                  |                      |                        |            |
|----------------|--------|------------------|----------------------|------------------------|------------|
| Catalog Number | Height | Package Quantity | Finish               | Type                   | Quick Ship |
| 23130-051      | 1200mm | 2                | Aluminum-Zinc Plated |                        | No         |
| 23130-056      | 2200mm | 2                | Aluminum-Zinc Plated | ETSI Panel Slide Mount | No         |
| 23130-055      | 2000mm | 2                | Aluminum-Zinc Plated | ETSI Panel Slide Mount | No         |
| 23130-054      | 1800mm | 2                | Aluminum-Zinc Plated | ETSI Panel Slide Mount | No         |
| 23130-053      | 1600mm | 2                | Aluminum-Zinc Plated | ETSI Panel Slide Mount | No         |
| 23130-052      | 1400mm | 2                | Aluminum-Zinc Plated | ETSI Panel Slide Mount | No         |

ADDITIONAL PRODUCT DETAILS

Shelves available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**