


# nVent ERICO Cadweld Exolon, Cable to Steel, HA, Steel Pipe, #2 Solid, 1 1/4"–2" Pipe

## Data Solutions

### CATALOG NUMBER

**XLHAA1T162C**



Developed in 1988, nVent ERICO Cadweld Exolon connections represented a significant advancement in welded electrical connections for sensitive indoor applications like data centers, hospitals, and other clean room environments. The virtual elimination of smoke and a unique electronic starting system makes this an ideal solution for sensitive applications. Each nVent ERICO Cadweld Exolon package contains ceramic filters that produce an extremely low emission connection.

### CERTIFICATIONS



### FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

### PRODUCT ATTRIBUTES

Mold Family: HA Mold Family

Connects To: Steel Pipe

Conductor Size: #2 Solid

Conductor Outer Diameter, Nominal: 6.53mm

Pipe Size: 1.25 – 2in

Outer Diameter (OD): 42.2 – 60.3mm

NB/DN: 32 – 50

Mold Split: None

Split Crucible: No

Wear Plates: No

Mold Only: No

Welding Material: XL45, Sold Separately

Handle Clamp: B323N2 or B320 and B322, Sold Separately

Frame: Attached

Price Key: XLA


Ease of Use: Preferred

## ADDITIONAL PRODUCT DETAILS

A test weld should be made to check for the possibility of burn through on thin sections and to determine detrimental metallurgical effects.

| W-XL-XX-X-XX-LH-XX-L-M |                                  |                                                                                                        |
|------------------------|----------------------------------|--------------------------------------------------------------------------------------------------------|
| W*                     | Wear Plates                      | Reduce mechanical abrasion of molds at cable entry points                                              |
| XL                     | ERICO CADWELD EXOLON Designation |                                                                                                        |
| XX                     | Mold Family                      |                                                                                                        |
| X                      | Price Key                        |                                                                                                        |
| XX                     | Conductor Size                   |                                                                                                        |
| LH                     | Weld End                         | LH = Weld on left end of conductor<br>RH = Weld on right end of conductor<br>(For VN Mold Family only) |
| XX                     | Pipe Size                        |                                                                                                        |
| L*                     | Split Crucible                   | Crucible section is split on molds designed with horizontal opening for easier cleaning                |
| M*                     | Mold Only                        |                                                                                                        |

\* Empty if none



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**