

# Dust Cap



Dust caps are installed into the end of the coupler to keep dirt and water out of the coupler cavity during transport and installation.

## FEATURES

Snug fit prevents the cap from falling out of the coupler

Easy to install and remove

## SPECIFICATIONS

**Material:** Polyethylene

Table 1/2

| Catalog Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Height (H) | Diameter 1 (Ø1) | Diameter 2 (Ø2) |
|----------------|--------------------|----------------|--------------------|------------|-----------------|-----------------|
| LK509          | 28 mm              | #9             | 30M                | 19 mm      | 55 mm           | 54 mm           |
| LK508          | 25 mm              | #8             | 25M                | 19 mm      | 52 mm           | 50 mm           |
| LK510          | 32 mm              | #10            |                    | 25 mm      | 59 mm           | 55 mm           |
| LK511          | 36 mm              | #11            | 35M                | 25 mm      | 63 mm           | 58 mm           |
| LK507          | 16 mm, 20 mm       | #5, #6, #7     | 15M, 20M           | 25 mm      | 49 mm           | 46 mm           |

Table 2/2


| Catalog Number | Color |
|----------------|-------|
|----------------|-------|

|       |      |
|-------|------|
| LK509 | Red  |
| LK508 | Red  |
| LK510 | Blue |
| LK511 | Blue |
| LK507 | Blue |

ADDITIONAL PRODUCT DETAILS

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**