

# NGC-40 Series, Control Module



The nVent RAYCHEM NGC-40-HTC (for single-phase heaters) and NGC-40-HTC3 (for three-phase heaters) modules are used to control either a solid-state relay or contactor within the NGC-40 control and monitoring system. This module also has one alarm output and one digital input. The alarm output can be used to control an external annunciator. The digital input is programmable and may be used for various functions such as forcing outputs on and off. Other features of this module include ground-fault and line current sensing for both HTC and HTC3. The front panel of the HTC module has LED indicators for various status conditions. The front panel also provides a ground-fault and heater test button.

## FEATURES

Din-rail mounted and part of the NGC-40 system

Individual single circuit control provides highest reliability for critical heat tracing circuits

Maximum design flexibility, by using the innovative data sharing among the heat tracing circuits within a panel, as well as, the programmable digital inputs and alarm outputs of each control module

Permanent supervision of the integrity of the heat tracing circuit and detailed problem reporting simplifies maintenance and increases personnel safety

## SPECIFICATIONS

|                               |              |
|-------------------------------|--------------|
| <b>Voltage Rating:</b>        | 24 V         |
| <b>Voltage Rating Type:</b>   | DC           |
| <b>Operating Temperature:</b> | -40 to 65 °C |

Table 1/1

| Catalog Number | Item Name   | Heat-Tracing Circuit |
|----------------|-------------|----------------------|
| 10730-004      | NGC-40-HTC3 | Three-Phase          |

| Catalog Number | Item Name  | Heat-Tracing Circuit |
|----------------|------------|----------------------|
| 10730-003      | NGC-40-HTC | Single-Phase         |

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Europe, Middle East, Africa**

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Asia Pacific**

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### **Latin America**

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**