

# Interscale Mounting Plate With Built-In Fan Holder and Fans

## Power Utilities

Interscale mounting plate with built-in fan holder and fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m3/h.

### FEATURES

Mounting plate (raised 4 mm) with integrated fan holder including fan kit for perforated case versions

Fans are simple to fit to the mounting plate using vibrationdamping fixing material

Mounting plate fixes into desktop case with 4 plastic feet or into 19" case with 4 screws

For technical data of fans, please see delivery includes

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth  | Height | Material | Product Family | Product Type   |
|----------------|--------|--------|--------|----------|----------------|----------------|
| 24827-105      | 444 mm | 177 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-107      | 444 mm | 310 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-154      | 221 mm | 177 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-155      | 221 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-175      | 310 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-195      | 399 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-197      | 399 mm | 310 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |

| CatalogNumber | Width  | Depth  | Height | Material | Product Family | Product Type   |
|---------------|--------|--------|--------|----------|----------------|----------------|
| 24827-255     | 221 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-275     | 310 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-295     | 399 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-297     | 399 mm | 310 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-375     | 310 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-395     | 399 mm | 221 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-397     | 399 mm | 310 mm | 1 mm   | Steel    | Interscale     | Mounting Plate |
| 24827-254     |        |        |        |          | Interscale     | Mounting Plate |
| 24827-205     |        |        |        |          |                | Mounting Plate |
| 24827-207     |        |        |        |          |                | Mounting Plate |
| 24827-305     |        |        |        |          |                | Mounting Plate |
| 24827-307     |        |        |        |          |                | Mounting Plate |

Table 2/2

| Catalog Number | Rack Width | Type           | Works With              |
|----------------|------------|----------------|-------------------------|
| 24827-105      | 19 HP      | Mounting Plate | Small Form Factor Cases |
| 24827-107      | 19 HP      | Mounting Plate | Small Form Factor Cases |
| 24827-154      |            | Mounting Plate | Small Form Factor Cases |
| 24827-155      |            | Mounting Plate | Small Form Factor Cases |
| 24827-175      |            | Mounting Plate | Small Form Factor Cases |

| Catalog Number | Rack Width | Type           | Works With              |
|----------------|------------|----------------|-------------------------|
| 24827-195      |            | Mounting Plate | Small Form Factor Cases |
| 24827-197      |            | Mounting Plate | Small Form Factor Cases |
| 24827-255      |            | Mounting Plate | Small Form Factor Cases |
| 24827-275      |            | Mounting Plate | Small Form Factor Cases |
| 24827-295      |            | Mounting Plate | Small Form Factor Cases |
| 24827-297      |            | Mounting Plate | Small Form Factor Cases |
| 24827-375      |            | Mounting Plate | Small Form Factor Cases |
| 24827-395      |            | Mounting Plate | Small Form Factor Cases |
| 24827-397      |            | Mounting Plate | Small Form Factor Cases |
| 24827-254      |            | Mounting Plate |                         |
| 24827-205      |            |                |                         |
| 24827-207      |            |                |                         |
| 24827-305      |            |                |                         |
| 24827-307      |            |                |                         |

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**