


# SNSW Flanged Nut



## FEATURES

Ideal for retrofit projects, such as trapeze installations, where disassembly of the support system is not desired

Use as a stopper when installing nVent CADDY Rod Lock assemblies

Can be easily installed, removed, and repositioned at any location along the threaded rod

Ready to use out of the box and eliminates multiple pieces of standard hardware

Functions as a hex nut and flat washer combined

Washer is wide enough to work with standard strut channel profiles

## SPECIFICATIONS

|                                   |                   |
|-----------------------------------|-------------------|
| <b>Static Load Safety Factor:</b> | 3:1               |
| <b>Finish:</b>                    | Electrogalvanized |
| <b>Material:</b>                  | Steel             |

Table 1/2

| Catalog Number | Article Number | Rod Size (RS) | Diameter (Ø) | Height (H) | Wrench Size | Flange Thickness (FT) |
|----------------|----------------|---------------|--------------|------------|-------------|-----------------------|
| SNSWM8         | 390101         | 8             | 42.4 mm      | 20mm       | 19 mm       | 6.5 mm                |
| SNSWM10        | 390102         | 10            | 42.4 mm      | 20mm       | 20 mm       | 6.5 mm                |

Table 2/2


| Catalog Number | Article Number | Static Load |
|----------------|----------------|-------------|
|----------------|----------------|-------------|

|         |        |       |
|---------|--------|-------|
| SNSWM8  | 390101 | 1557N |
| SNSWM10 | 390102 | 1557N |

### ADDITIONAL PRODUCT DETAILS

For use on plain and electro zinc plated hardware only.

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

