

# nVent ERICO Cadweld Exolon, Cable to Cable

## Data Solutions



Developed in 1988, nVent ERICO Cadweld Exolon connections represented a significant advancement in welded electrical connections for sensitive indoor applications like data centers, hospitals, and other clean room environments. The virtual elimination of smoke and a unique electronic starting system makes this an ideal solution for sensitive applications. Each nVent ERICO Cadweld Exolon package contains ceramic filters that produce an extremely low emission connection.

### CERTIFICATIONS



### FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

### SPECIFICATIONS

Table 1/1

| Catalog Number | Mold Family | Conductor 1 | Conductor 1 Outer Diameter, Nominal | Conductor 2 | Conductor 2 Outer Diameter, Nominal | Certifications |
|----------------|-------------|-------------|-------------------------------------|-------------|-------------------------------------|----------------|
|----------------|-------------|-------------|-------------------------------------|-------------|-------------------------------------|----------------|

|            |                |                |         |               |        |         |
|------------|----------------|----------------|---------|---------------|--------|---------|
| XLTAC2G1H  | TA Mold Family | 2/0 Concentric | 10.62mm | #6 Concentric | 4.67mm | cUL, UL |
| XLTAC2Q1H  | TA Mold Family | 4/0 Concentric | 13.41mm | #6 Concentric | 4.67mm | UL, cUL |
| XLPPC1V1H  | PC Mold Family | #2 Concentric  | 7.42mm  | #6 Concentric | 4.67mm | cUL, UL |
| XLPPC2C1H  | PC Mold Family | 1/0 Concentric | 9.47mm  | #6 Concentric | 4.67mm | UL, cUL |
| XLPPC2G1H  | PC Mold Family | 2/0 Concentric | 10.62mm | #6 Concentric | 4.67mm | cUL, UL |
| XLPPC2Q1H  | PC Mold Family | 4/0 Concentric | 13.41mm | #6 Concentric | 4.67mm | cUL, UL |
| XLPGP1H1H  | PG Mold Family | #6 Concentric  | 4.67mm  | #6 Concentric | 4.67mm | UL, cUL |
| XLPGP1H1HM | PG Mold Family | #6 Concentric  | 4.67mm  | #6 Concentric | 4.67mm | cUL, UL |
| XLPTC1L1H  | PT Mold Family | #4 Concentric  | 5.89mm  | #6 Concentric | 4.67mm | cUL, UL |
| XLPTC2Q1H  | PT Mold Family | 4/0 Concentric | 13.41mm | #6 Concentric | 4.67mm | cUL, UL |
| XLTAC1H1H  | TA Mold Family | #6 Concentric  | 4.67mm  | #6 Concentric | 4.67mm | UL, cUL |
| XLPPC2C1L  | PC Mold Family | 1/0 Concentric | 9.47mm  | #4 Concentric | 5.89mm | cUL, UL |
| XLPPC2G1L  | PC Mold Family | 2/0 Concentric | 10.62mm | #4 Concentric | 5.89mm | UL, cUL |
| XLPPC2Q1L  | PC Mold Family | 4/0 Concentric | 13.41mm | #4 Concentric | 5.89mm | cUL, UL |
| XLPTC1L1L  | PT Mold Family | #4 Concentric  | 5.89mm  | #4 Concentric | 5.89mm | UL, cUL |
| XLPTC2C1L  | PT Mold Family | 1/0 Concentric | 9.47mm  | #4 Concentric | 5.89mm | cUL, UL |
| XLSSC1L    | SS Mold Family | #4 Concentric  | 5.89mm  | #4 Concentric | 5.89mm | cUL, UL |
| XLTAC1L1L  | TA Mold Family | #4 Concentric  | 5.89mm  | #4 Concentric | 5.89mm | cUL, UL |
| XLTAC2Q1L  | TA Mold Family | 4/0 Concentric | 13.41mm | #4 Concentric | 5.89mm | UL, cUL |

|           |                |                               |         |                               |        |         |
|-----------|----------------|-------------------------------|---------|-------------------------------|--------|---------|
| XLTAC3D1L | TA Mold Family | 350 kcmil Concentric          | 17.3mm  | #4 Concentric                 | 5.89mm |         |
| XLXBC1V1L | XB Mold Family | #2 Concentric                 | 7.42mm  | #4 Concentric                 | 5.89mm | cUL, UL |
| XLTAC2Q1T | TA Mold Family | 4/0 Concentric                | 13.41mm | #2 Solid                      | 6.53mm | cUL, UL |
| XLSSC1T   | SS Mold Family | #2 Solid                      | 6.53mm  | #2 Solid                      | 6.53mm | UL, cUL |
| XLPPC2Q1V | PC Mold Family | 4/0 Concentric                | 13.41mm | #2 Concentric                 | 7.42mm | UL, cUL |
| XLPTC2G1V | PT Mold Family | 2/0 Concentric                | 10.62mm | #2 Concentric                 | 7.42mm | cUL, UL |
| XLSSC1V   | SS Mold Family | #2 Concentric                 | 7.42mm  | #2 Concentric                 | 7.42mm | cUL, UL |
| XLTAC1V1V | TA Mold Family | #2 Concentric                 | 7.42mm  | #2 Concentric                 | 7.42mm | UL, cUL |
| XLTAC2C1V | TA Mold Family | 1/0 Concentric                | 9.47mm  | #2 Concentric                 | 7.42mm | UL, cUL |
| XLTAC2G1V | TA Mold Family | 2/0 Concentric                | 10.62mm | #2 Concentric                 | 7.42mm | UL, cUL |
| XLTAC2L1V | TA Mold Family | 3/0 Concentric                | 11.94mm | #2 Concentric                 | 7.42mm | cUL, UL |
| XLTAC2Q1V | TA Mold Family | 4/0 Concentric                | 13.41mm | #2 Concentric                 | 7.42mm | UL, cUL |
| XLTCR3X1V | TC Mold Family | 600 kcmil Concentric          | 22.68mm | #2 Concentric                 | 7.42mm |         |
| XLXBC1V1V | XB Mold Family | #2 Concentric                 | 7.42mm  | #2 Concentric                 | 7.42mm | UL, cUL |
| XLXBM2G1V | XB Mold Family | 2/0 Concentric                | 10.62mm | #2 Concentric                 | 7.42mm | cUL, UL |
| XLPTC1Y1Y | PT Mold Family | #1 Concentric                 | 8.43mm  | #1 Concentric                 | 8.43mm | cUL, UL |
| XLSSC1Y   | SS Mold Family | #1 Concentric                 | 8.43mm  | #1 Concentric                 | 8.43mm | cUL, UL |
| XLTACY3Y3 | TA Mold Family | 50 mm <sup>2</sup> Concentric | 8.99mm  | 50 mm <sup>2</sup> Concentric | 8.99mm | UL, cUL |
| XLTAC2C2C | TA Mold Family | 1/0 Concentric                | 9.47mm  | 1/0 Concentric                | 9.47mm | cUL, UL |

|            |                |                      |         |                |         |         |
|------------|----------------|----------------------|---------|----------------|---------|---------|
| XLTAC2C2L  | TA Mold Family | 1/0 Concentric       | 9.47mm  | 3/0 Concentric | 11.94mm | UL, cUL |
| XLTAC2C2Q  | TA Mold Family | 1/0 Concentric       | 9.47mm  | 4/0 Concentric | 13.41mm | UL, cUL |
| XLTAC2L2C  | TA Mold Family | 3/0 Concentric       | 11.94mm | 1/0 Concentric | 9.47mm  | UL, cUL |
| XLTAC2Q2C  | TA Mold Family | 1/0 Concentric       | 9.47mm  | 4/0 Concentric | 13.41mm | UL, cUL |
| XLTAC3D2C  | TA Mold Family | 350 kcmil Concentric | 17.3mm  | 1/0 Concentric | 9.47mm  |         |
| XLXBM2C2C  | XB Mold Family | 1/0 Concentric       | 9.47mm  | 1/0 Concentric | 9.47mm  | cUL, UL |
| XLPTC2C2C  | PT Mold Family | 1/0 Concentric       | 9.47mm  | 1/0 Concentric | 9.47mm  | UL, cUL |
| XLPTC2G2C  | PT Mold Family | 2/0 Concentric       | 10.62mm | 1/0 Concentric | 9.47mm  | cUL, UL |
| XLPTC2L2C  | PT Mold Family | 3/0 Concentric       | 11.94mm | 1/0 Concentric | 9.47mm  | cUL, UL |
| XLPTC2Q2C  | PT Mold Family | 4/0 Concentric       | 13.41mm | 1/0 Concentric | 9.47mm  | cUL, UL |
| XLPTC2Q2CW | PT Mold Family | 4/0 Concentric       | 13.41mm | 1/0 Concentric | 9.47mm  | UL, cUL |
| XLSSC2C    | SS Mold Family | 1/0 Concentric       | 9.47mm  | 1/0 Concentric | 9.47mm  | UL, cUL |
| XLPTC2G2G  | PT Mold Family | 2/0 Concentric       | 10.62mm | 2/0 Concentric | 10.62mm | UL, cUL |
| XLPTC2L2G  | PT Mold Family | 3/0 Concentric       | 11.94mm | 2/0 Concentric | 10.62mm | cUL, UL |
| XLPTC2Q2G  | PT Mold Family | 4/0 Concentric       | 13.41mm | 2/0 Concentric | 10.62mm | cUL, UL |
| XLSSC2G    | SS Mold Family | 2/0 Concentric       | 10.62mm | 2/0 Concentric | 10.62mm | cUL, UL |
| XLTAC2G2G  | TA Mold Family | 2/0 Concentric       | 10.62mm | 2/0 Concentric | 10.62mm | UL, cUL |
| XLTAC2L2G  | TA Mold Family | 3/0 Concentric       | 11.94mm | 2/0 Concentric | 10.62mm | UL, cUL |
| XLTAC2Q2G  | TA Mold Family | 4/0 Concentric       | 13.41mm | 2/0 Concentric | 10.62mm | cUL, UL |

|             |                |                                  |         |                                  |         |         |
|-------------|----------------|----------------------------------|---------|----------------------------------|---------|---------|
| XLXBM2Q2G   | XB Mold Family | 4/0 Concentric                   | 13.41mm | 2/0 Concentric                   | 10.62mm | cUL, UL |
| XLPTCY4Y4   | PT Mold Family | 70 mm <sup>2</sup><br>Concentric | 10.92mm | 70 mm <sup>2</sup><br>Concentric | 10.92mm |         |
| XLTACY4Y4   | TA Mold Family | 70 mm <sup>2</sup><br>Concentric | 10.92mm | 70 mm <sup>2</sup><br>Concentric | 10.92mm | cUL, UL |
| XLTAC2L2L   | TA Mold Family | 3/0 Concentric                   | 11.94mm | 3/0 Concentric                   | 11.94mm | cUL, UL |
| XLTAC2Q2L   | TA Mold Family | 4/0 Concentric                   | 13.41mm | 3/0 Concentric                   | 11.94mm | UL, cUL |
| XLTAC3Q2L   | TA Mold Family | 500 kcmil<br>Concentric          | 20.65mm | 3/0 Concentric                   | 11.94mm |         |
| XLXBM2L2L   | XB Mold Family | 3/0 Concentric                   | 11.94mm | 3/0 Concentric                   | 11.94mm | UL, cUL |
| XLPTC2L2L   | PT Mold Family | 3/0 Concentric                   | 11.94mm | 3/0 Concentric                   | 11.94mm | UL, cUL |
| XLSSC2L     | SS Mold Family | 3/0 Concentric                   | 11.94mm | 3/0 Concentric                   | 11.94mm | cUL, UL |
| XLSVR2L     | SV Mold Family | 3/0 Concentric                   | 11.94mm | 3/0 Concentric                   | 11.94mm |         |
| XLPC3Q2Q    | PC Mold Family | 500 kcmil<br>Concentric          | 20.65mm | 4/0 Concentric                   | 13.41mm | cUL, UL |
| XLPC3Q2QS   | PC Mold Family | 500 kcmil<br>Concentric          | 20.65mm | 4/0 Concentric                   | 13.41mm | cUL, UL |
| XLPTC2Q2Q   | PT Mold Family | 4/0 Concentric                   | 13.41mm | 4/0 Concentric                   | 13.41mm | cUL, UL |
| XLPTC2Q2QS  | PT Mold Family | 4/0 Concentric                   | 13.41mm | 4/0 Concentric                   | 13.41mm | UL, cUL |
| XLPTC2V2Q   | PT Mold Family | 250 kcmil<br>Concentric          | 14.61mm | 4/0 Concentric                   | 13.41mm | cUL, UL |
| XLSSC2Q     | SS Mold Family | 4/0 Concentric                   | 13.41mm | 4/0 Concentric                   | 13.41mm | UL, cUL |
| XLXBM2Q2Q   | XB Mold Family | 4/0 Concentric                   | 13.41mm | 4/0 Concentric                   | 13.41mm | cUL, UL |
| XLXBM2Q2QMS | XB Mold Family | 4/0 Concentric                   | 13.41mm | 4/0 Concentric                   | 13.41mm | UL, cUL |
| XLXBM2Q2QS  | XB Mold Family | 4/0 Concentric                   | 13.41mm | 4/0 Concentric                   | 13.41mm | cUL, UL |

|                  |                |                         |         |                         |         |         |
|------------------|----------------|-------------------------|---------|-------------------------|---------|---------|
| XLXBM2Q2QWS      | XB Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | cUL, UL |
| XLXBQ2Q2Q        | XB Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | UL, cUL |
| XLXBQ2Q2QS       | XB Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | cUL, UL |
| XLXBQ2Q2QW       | XB Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | cUL, UL |
| XLXBQ2Q2QWS      | XB Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | UL, cUL |
| XLTAC2Q2Q        | TA Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | UL, cUL |
| XLTAC2Q2QW       | TA Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm | cUL, UL |
| XLTAC2Q9FW       | TA Mold Family | 4/0 Concentric          | 13.41mm | 19/#9<br>Copperweld     | 14.53mm |         |
| XLTAC2V2Q        | TA Mold Family | 250 kcmil<br>Concentric | 14.61mm | 4/0 Concentric          | 13.41mm | cUL, UL |
| XLTAC3Q2Q        | TA Mold Family | 500 kcmil<br>Concentric | 20.65mm | 4/0 Concentric          | 13.41mm |         |
| XLTAC3Q2QW       | TA Mold Family | 500 kcmil<br>Concentric | 20.65mm | 4/0 Concentric          | 13.41mm |         |
| XLTAC9F2QW       | TA Mold Family | 19/#9<br>Copperweld     | 14.53mm | 4/0 Concentric          | 13.41mm |         |
| XLTCR2Q2Q        | TC Mold Family | 4/0 Concentric          | 13.41mm | 4/0 Concentric          | 13.41mm |         |
| XLTCR2V2Q        | TC Mold Family | 250 kcmil<br>Concentric | 14.61mm | 4/0 Concentric          | 13.41mm |         |
| XLTAC3Q2V        | TA Mold Family | 500 kcmil<br>Concentric | 20.65mm | 250 kcmil<br>Concentric | 14.61mm |         |
| XLTAC9F9FW       | TA Mold Family | 19/#9<br>Copperweld     | 14.53mm | 19/#9<br>Copperweld     | 14.53mm |         |
| XLHDTAC3D3D      | TA Mold Family | 350 kcmil<br>Concentric | 17.3mm  | 350 kcmil<br>Concentric | 17.3mm  |         |
| XLHDTAC3D3D<br>S | TA Mold Family | 350 kcmil<br>Concentric | 17.3mm  | 350 kcmil<br>Concentric | 17.3mm  |         |
| XLTAC3Q3D        | TA Mold Family | 500 kcmil<br>Concentric | 20.65mm | 350 kcmil<br>Concentric | 17.3mm  |         |

|             |                |                      |         |                      |         |  |
|-------------|----------------|----------------------|---------|----------------------|---------|--|
| XLTAC3Q3H   | TA Mold Family | 500 kcmil Concentric | 20.65mm | 400 kcmil Concentric | 18.49mm |  |
| XLTAC3Q3HS  | TA Mold Family | 500 kcmil Concentric | 20.65mm | 400 kcmil Concentric | 18.49mm |  |
| XLTAC3Q3Q   | TA Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLTAC3Q3QS  | TA Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLTAD3Q3QS  | TA Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLTCF3Q3QW  | TC Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLTCF3Q3QWS | TC Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLPTD3Q3Q   | PT Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLPTD3Q3QS  | PT Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLSSC3Q     | SS Mold Family | 500 kcmil Concentric | 20.65mm | 500 kcmil Concentric | 20.65mm |  |
| XLSSC4L     | SS Mold Family | 750 kcmil Concentric | 25.35mm | 750 kcmil Concentric | 25.35mm |  |

## ADDITIONAL PRODUCT DETAILS

A gap between conductors may be required. See mold tag for more information.

| XL-XX-X-XX-XX-L-M-W |                                  |                                                                                         |
|---------------------|----------------------------------|-----------------------------------------------------------------------------------------|
| XL                  | ERICO CADWELD EXOLON Designation |                                                                                         |
| XX                  | Mold Family                      |                                                                                         |
| X                   | Price Key                        |                                                                                         |
| XX                  | Conductor Code 1                 |                                                                                         |
| XX                  | Conductor Code 2                 |                                                                                         |
| L*                  | Split Crucible                   | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M*                  | Mold Only                        |                                                                                         |
| W*                  | Wear Plates                      | Reduce mechanical abrasion of molds at cable entry points                               |

\* Empty if none

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**