

# Varistar CP Telescopic Tip-Over Protection

Telescopic Tip-Over Protection for ballance protection with 150Kg at full extension and lateral and rear cable management possibilities.



## FEATURES

Telescopic Tip-Over Protection with max. 150 kg at full extension

Lateral and rear cable entry possible

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Material:** Steel

Table 1/2

| Catalog Number | Height | Width | Depth  | Package Quantity | Color      | Color Code |
|----------------|--------|-------|--------|------------------|------------|------------|
| 24630-085      | 100mm  | 600mm | 900mm  | 1                | Black Grey | RAL 7021   |
| 24630-087      | 200mm  | 600mm | 900mm  | 1                | Black Grey | RAL 7021   |
| 24630-044      | 100mm  | 600mm | 1000mm | 1                | Black Grey | RAL 7021   |
| 24630-050      | 200mm  | 600mm | 1000mm | 1                | Black Grey | RAL 7021   |
| 24630-045      | 100mm  | 600mm | 1100mm | 1                | Black Grey | RAL 7021   |
| 24630-051      | 200mm  | 600mm | 1100mm | 1                | Black Grey | RAL 7021   |

| CatalogNumber | Height | Width | Depth  | Package Quantity | Color      | Color Code |
|---------------|--------|-------|--------|------------------|------------|------------|
| 24630-046     | 100mm  | 600mm | 1200mm | 1                | Black Grey | RAL 7021   |
| 24630-052     | 200mm  | 600mm | 1200mm | 1                | Black Grey | RAL 7021   |
| 24630-086     | 100mm  | 800mm | 900mm  | 1                | Black Grey | RAL 7021   |
| 24630-088     | 200mm  | 800mm | 900mm  | 1                | Black Grey | RAL 7021   |
| 24630-047     | 100mm  | 800mm | 1000mm | 1                | Black Grey | RAL 7021   |
| 24630-053     | 200mm  | 800mm | 1000mm | 1                | Black Grey | RAL 7021   |
| 24630-048     | 100mm  | 800mm | 1100mm | 1                | Black Grey | RAL 7021   |
| 24630-054     | 200mm  | 800mm | 1100mm | 1                | Black Grey | RAL 7021   |
| 24630-049     | 100mm  | 800mm | 1200mm | 1                | Black Grey | RAL 7021   |
| 24630-055     | 200mm  | 800mm | 1200mm | 1                | Black Grey | RAL 7021   |

| Table 2/2      |               |                     |            |
|----------------|---------------|---------------------|------------|
| Catalog Number | Finish        | Type                | Quick Ship |
| 24630-085      | Powder Coated | Tip-Over Protection | No         |
| 24630-087      | Powder Coated | Tip-Over Protection | No         |
| 24630-044      | Powder Coated | Tip-Over Protection | No         |
| 24630-050      | Powder Coated | Tip-Over Protection | No         |
| 24630-045      | Powder Coated | Tip-Over Protection | No         |
| 24630-051      | Powder Coated | Tip-Over Protection | No         |
| 24630-046      | Powder Coated | Tip-Over Protection | No         |

| Catalog Number | Finish        | Type                | Quick Ship |
|----------------|---------------|---------------------|------------|
| 24630-052      | Powder Coated | Tip-Over Protection | No         |
| 24630-086      | Powder Coated | Tip-Over Protection | No         |
| 24630-088      | Powder Coated | Tip-Over Protection | No         |
| 24630-047      | Powder Coated | Tip-Over Protection | No         |
| 24630-053      | Powder Coated | Tip-Over Protection | No         |
| 24630-048      | Powder Coated | Tip-Over Protection | No         |
| 24630-054      | Powder Coated | Tip-Over Protection | No         |
| 24630-049      | Powder Coated | Tip-Over Protection | No         |
| 24630-055      | Powder Coated | Tip-Over Protection | No         |

## ADDITIONAL PRODUCT DETAILS

---

Only for use in conjunction with plinth or mobile plinth.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**