


# C-Profile Adaptor for Subracks Assembled into Cabinets



The C-profile, assembled on the Side Panel of the subrack serves to fix the subrack on the guiding profile when mounted into a cabinet.

## CERTIFICATIONS



## FEATURES

The C-profile fixes the subrack on the guiding profile when mounted into a cabinet.

## SPECIFICATIONS

|                        |                  |
|------------------------|------------------|
| <b>Material:</b>       | Aluminum         |
| <b>Finish:</b>         | Anodized         |
| <b>Product Family:</b> | EuropacPRO       |
| <b>Product Type:</b>   | Telescopic Slide |

Table 1/1

| Catalog Number | Depth | Package Quantity | Works With | Quick Ship |
|----------------|-------|------------------|------------|------------|
| 24562-453      | 175mm | 2                | Subracks   | No         |
| 24562-454      | 235mm | 2                | Subracks   | No         |
| 24562-455      | 295mm | 2                | Subracks   | No         |

| Catalog Number | Depth | Package Quantity | Works With | Quick Ship |
|----------------|-------|------------------|------------|------------|
| 24562-456      | 355mm | 2                | Subracks   | No         |
| 24562-457      | 415mm | 2                | Subracks   | No         |
| 24562-458      | 475mm | 2                | Subracks   | No         |

## ADDITIONAL PRODUCT DETAILS

Note: No end stop when pulling out the subrack.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**