

Varistar CP Side Panel With Quick-Release Fastener and Lock

Varistar Side Panels with Quick-Release Fastener without grounding kit.



FEATURES

Steel, 1 mm

Side panel without grounding kit

Safety lock kit included

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Protection Rating: IP20

Table 1/2

| Catalog Number | Rack Height | Height | Depth | Package Quantity | Color | Color Code |
|----------------|-------------|--------|-------|------------------|------------|------------|
| 21630-285 | 24U | 1200mm | 600mm | 2 | Black Grey | RAL 7021 |
| 21630-286 | 24U | 1200mm | 800mm | 2 | Black Grey | RAL 7021 |
| 21630-289 | 29U | 1400mm | 600mm | 2 | Black Grey | RAL 7021 |
| 21630-290 | 29U | 1400mm | 800mm | 2 | Black Grey | RAL 7021 |
| 21630-293 | 33U | 1600mm | 600mm | 2 | Black Grey | RAL 7021 |

| CatalogNumber | Rack Height | Height | Depth | Package Quantity | Color | Color Code |
|---------------|-------------|--------|--------|------------------|------------|------------|
| 21630-294 | 33U | 1600mm | 800mm | 2 | Black Grey | RAL 7021 |
| 21630-297 | 38U | 1800mm | 600mm | 2 | Black Grey | RAL 7021 |
| 21630-298 | 38U | 1800mm | 800mm | 2 | Black Grey | RAL 7021 |
| 21630-302 | 42U | 2000mm | 600mm | 2 | Black Grey | RAL 7021 |
| 21630-303 | 42U | 2000mm | 800mm | 2 | Black Grey | RAL 7021 |
| 21630-304 | 42U | 2000mm | 900mm | 2 | Black Grey | RAL 7021 |
| 21630-306 | 47U | 2200mm | 600mm | 2 | Black Grey | RAL 7021 |
| 21630-307 | 47U | 2200mm | 800mm | 2 | Black Grey | RAL 7021 |
| 21630-308 | 47U | 2200mm | 900mm | 2 | Black Grey | RAL 7021 |
| 21630-287 | 24U | 1200mm | 900mm | 2 | Black Grey | RAL 7021 |
| 21630-288 | 24U | 1200mm | 1000mm | 2 | Black Grey | RAL 7021 |
| 21630-291 | 29U | 1400mm | 900mm | 2 | Black Grey | RAL 7021 |
| 21630-292 | 29U | 1400mm | 1000mm | 2 | Black Grey | RAL 7021 |
| 21630-295 | 33U | 1600mm | 900mm | 2 | Black Grey | RAL 7021 |
| 21630-296 | 33U | 1600mm | 1000mm | 2 | Black Grey | RAL 7021 |
| 21630-299 | 38U | 1800mm | 900mm | 2 | Black Grey | RAL 7021 |
| 21630-300 | 38U | 1800mm | 1000mm | 2 | Black Grey | RAL 7021 |

Table 2/2

| Catalog Number | Finish | Material | Type | Quick Ship |
|----------------|--------|----------|------|------------|
|----------------|--------|----------|------|------------|

| | | | | |
|-----------|---------------|-------|---------------------------|----|
| 21630-285 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-286 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-289 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-290 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-293 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-294 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-297 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-298 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-302 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-303 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-304 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-306 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-307 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-308 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-287 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-288 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-291 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-292 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-295 | Powder Coated | Steel | Side Panel, Quick Release | No |

| | | | | |
|-----------|---------------|-------|---------------------------|----|
| 21630-296 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-299 | Powder Coated | Steel | Side Panel, Quick Release | No |
| 21630-300 | Powder Coated | Steel | Side Panel, Quick Release | No |

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE