


Novastar Rear Panel With Cable Ducting



Novastar Rear Panel with 3 U or 4 U cable ducting for improved cable management.

CERTIFICATIONS



FEATURES

Cable ducting and door hinge bracket

Cable ducting can be fitted at top or bottom

2 twist-locking catches (Torx T30, with 1/4 turn)

Incl. grounding

St, 1 mm

3 U cable ducting for cabinet heights 16, 20, 38, 47 U; 4 U cable ducting for cabinet heights 25, 34, 43 U

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Material
----------------	-------------	--------	-------	-------	------------	----------

25230-426	12U	555mm	553mm	Black Grey	RAL 7021	Steel
25230-430	16U	733mm	553mm	Black Grey	RAL 7021	Steel
25230-434	20U	911mm	553mm	Black Grey	RAL 7021	Steel
25230-439	25U	1133mm	553mm	Black Grey	RAL 7021	Steel
25230-448	34U	1534mm	553mm	Black Grey	RAL 7021	Steel
25230-452	38U	1711mm	553mm	Black Grey	RAL 7021	Steel
25230-457	43U	1933mm	553mm	Black Grey	RAL 7021	Steel
25230-461	47U	2111mm	553mm	Black Grey	RAL 7021	Steel
26230-426	12U	555mm	553mm	Black Grey	RAL 7021	Steel
26230-430	16U	733mm	553mm	Light Grey	RAL 7035	Steel
26230-434	20U	911mm	553mm	Light Grey	RAL 7035	Steel
26230-439	25U	1133mm	553mm	Light Grey	RAL 7035	Steel
26230-448	34U	1534mm	553mm	Light Grey	RAL 7035	Steel
26230-452	38U	1711mm	553mm	Light Grey	RAL 7035	Steel
26230-457	43U	1933mm	553mm	Light Grey	RAL 7035	Steel
26230-461	47U	2111mm	553mm	Light Grey	RAL 7035	Steel
25230-443	29U	1345mm	553mm	Black Grey	RAL 7021	Steel
26230-443	29U	1345mm	553mm	Light Grey	RAL 7035	Steel

Table 2/2

Catalog Number	Package Quantity	Finish	Type	Certifications	Quick Ship
----------------	------------------	--------	------	----------------	------------

25230-426	1	Powder Coated	Rear Panel	RoHS	No
25230-430	1	Powder Coated	Rear Panel	RoHS	No
25230-434	1	Powder Coated	Rear Panel	RoHS	No
25230-439	1	Powder Coated	Rear Panel	RoHS	No
25230-448	1	Powder Coated	Rear Panel	RoHS	No
25230-452	1	Powder Coated	Rear Panel	RoHS	No
25230-457	1	Powder Coated	Rear Panel	RoHS	No
25230-461	1	Powder Coated	Rear Panel	RoHS	No
26230-426	1	Powder Coated	Rear Panel	RoHS	No
26230-430	1	Powder Coated	Rear Panel	RoHS	No
26230-434	1	Powder Coated	Rear Panel	RoHS	No
26230-439	1	Powder Coated	Rear Panel	RoHS	No
26230-448	1	Powder Coated	Rear Panel	RoHS	No
26230-452	1	Powder Coated	Rear Panel	RoHS	No
26230-457	1	Powder Coated	Rear Panel	RoHS	No
26230-461	1	Powder Coated	Rear Panel	RoHS	No
25230-443	1	Powder Coated	Rear Panel		No
26230-443	1	Powder Coated	Rear Panel		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE