


# Varistar Cable Panel



Vertical cable panel for Varistar free standing cabinets powdered in cabinet color in different widths.

## CERTIFICATIONS



## FEATURES

For fitting directly onto the frame

Cables are assembled in place with cable ties or Velcro

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height  | Width | Depth | Package Quantity | Color      |
|----------------|-------------|---------|-------|-------|------------------|------------|
| 23130-499      |             | 915.5mm | 110mm | 10mm  | 2                | Black Grey |
| 23130-500      |             | 604mm   | 110mm | 10mm  | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Depth | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------|------------------|------------|
| 23130-501     |             | 446mm  | 110mm | 10mm  | 2                | Black Grey |
| 23130-502     |             | 1019mm | 110mm | 10mm  | 2                | Black Grey |
| 23130-503     |             | 670mm  | 110mm | 10mm  | 2                | Black Grey |
| 23130-504     |             | 496mm  | 110mm | 10mm  | 2                | Black Grey |
| 23130-150     | 42U         | 2000mm | 250mm | 250mm | 2                | Black Grey |
| 23130-151     | 47U         | 2200mm | 250mm | 250mm | 2                | Black Grey |
| 23130-420     | 38U         | 1800mm | 150mm | 150mm | 2                | Black Grey |
| 23130-421     | 42U         | 2000mm | 150mm | 150mm | 2                | Black Grey |
| 23130-422     | 47U         | 2200mm | 150mm | 150mm | 2                | Black Grey |
| 23130-625     | 52U         | 2450mm | 250mm | 250mm | 2                | Black Grey |
| 23130-628     | 52U         | 2450mm | 150mm | 150mm | 2                | Black Grey |

| Table 2/2      |            |               |             |            |
|----------------|------------|---------------|-------------|------------|
| Catalog Number | Color Code | Finish        | Type        | Quick Ship |
| 23130-499      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-500      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-501      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-502      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-503      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-504      | RAL 7021   | Powder Coated | Cable Panel | No         |

| Catalog Number | Color Code | Finish        | Type        | Quick Ship |
|----------------|------------|---------------|-------------|------------|
| 23130-150      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-151      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-420      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-421      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-422      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-625      | RAL 7021   | Powder Coated | Cable Panel | No         |
| 23130-628      | RAL 7021   | Powder Coated | Cable Panel | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**