



Male-Male Adaptor, Imperial Thread



CERTIFICATIONS



FEATURES

Threaded adaptor with hexagonal body for ease of tightening

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Thread Size 1 (TS1)	Thread Size 2 (TS2)	Height (H)	Width (W)	Unit Weight
LPS2955M5M	Stainless Steel 304 (EN 1.4301)	5/8" UNC	5/8" UNC	38.1 mm	19.1 mm	0.02 kg
LPC2955M5M	Copper	5/8" UNC	5/8" UNC	38.1 mm	19.1 mm	0.02 kg
LPA2942M5M	Aluminum	1/2" UNC	5/8" UNC	38.1 mm	19.1 mm	0.02 kg
LPC2945M2M	Copper	5/8" UNC	1/2" UNC	38.1 mm	19.1 mm	0.02 kg
LPA2955M5M	Aluminum	5/8" UNC	5/8" UNC	38.1 mm	19.1 mm	0.02 kg


CatalogNumber	Material	Thread Size 1 (TS1)	Thread Size 2 (TS2)	Height (H)	Width (W)	Unit Weight
LPS2932M2M	Stainless Steel 304 (EN 1.4301)	1/2" UNC	1/2" UNC	38.1 mm	19.1 mm	0.02 kg
LPC2932M2M	Copper	1/2" UNC	1/2" UNC	38.1 mm	19.1 mm	0.02 kg
LPA2932M2M	Aluminum	1/2" UNC	1/2" UNC	38.1 mm	19.1 mm	0.02 kg
LPC2913M3M	Copper	3/8" UNC	3/8" UNC	38.1 mm	19.1 mm	0.02 kg
LPS2945M2M	Stainless Steel 304 (EN 1.4301)	5/8" UNC	1/2" UNC	38.1 mm	19.1 mm	0.02 kg
LPC2922M3M	Copper	1/2" UNC	3/8" UNC	38.1 mm	19.1 mm	0.02 kg

Table 2/2

Catalog Number	Certifications
LPS2955M5M	
LPC2955M5M	E202878-Combined_CoC, E202878-Combined_CoC
LPA2942M5M	E202878-Combined_CoC, E202878-Combined_CoC
LPC2945M2M	E202878-Combined_CoC, E202878-Combined_CoC
LPA2955M5M	
LPS2932M2M	
LPC2932M2M	E202878-Combined_CoC, E202878-Combined_CoC
LPA2932M2M	E202878-Combined_CoC, E202878-Combined_CoC
LPC2913M3M	E202878-Combined_CoC, E202878-Combined_CoC
LPS2945M2M	

Catalog Number	Certifications
LPC2922M3M	E202878-Combined_CoC, E202878-Combined_CoC

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ **WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE