


# Air Terminal Base, Stamped Narrow, Imperial Thread



## CERTIFICATIONS



## FEATURES

For use on narrow flat surfaces

Positive single bolt tension for multi-directional cable clamping

## SPECIFICATIONS

**Conductor Size, UL:** Class 1 - Class 2 (4/0 Max)

Table 1/2


Catalog Number	Material	Finish	Thread Size (TS)	Hole Size (HS)	Depth (D)	Height (H)
LPA30412	Aluminum		1/2" UNC	5 mm	54mm	42 mm
LPA30458	Aluminum		5/8" UNC	5 mm	54mm	42 mm
LPC30412	Copper		1/2" UNC	5 mm	54mm	42 mm

CatalogNumber	Material	Finish	Thread Size (TS)	Hole Size (HS)	Depth (D)	Height (H)
LPC30438	Copper		3/8" UNC	5 mm	54mm	42 mm
LPC30458	Copper		5/8" UNC	5 mm	54mm	42 mm
LPC304L12	Copper	Tinned	1/2" UNC	5 mm	54mm	42 mm
LPC304L38	Copper	Tinned	3/8" UNC	5 mm	54mm	42 mm
LPC304L58	Copper	Tinned	5/8" UNC	5 mm	54mm	42 mm

Table 2/2

Catalog Number	Width (W)	Unit Weight
LPA30412	108 mm	0.04 kg
LPA30458	108 mm	0.04 kg
LPC30412	108 mm	0.11 kg
LPC30438	108 mm	0.11 kg
LPC30458	108 mm	0.11 kg
LPC304L12	108 mm	0.11 kg
LPC304L38	108 mm	0.11 kg
LPC304L58	108 mm	0.11 kg

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠** WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**