

Concept Panels



Concept panels are taller and wider than corresponding NEMA-size panels.

FEATURES

Painted white or conductive finish

Include a formed flange along any side that is longer than 22.20 in (564 mm)

Optional wood panels are made of 3/4-in plywood, pre-cut and pre-drilled to install on panel mounting studs in the rear of the cabinet

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP2020W	23785	462mm	462mm	Plywood	Smooth Matte	
CP3220W	23786	767mm	462mm	Plywood	Smooth Matte	
CP4420W	23787	1072mm	462mm	Plywood	Smooth Matte	
CP1210	29664	259mm	208mm	Mild Steel	Powder Coated	White
CP1210G	29665	259mm	208mm	Mild Steel	Galvanized	
CP1212	78510	259mm	259mm	Mild Steel	Powder Coated	White
CP2020	78550	462mm	462mm	Mild Steel	Powder Coated	White
CP2020G	15051	462mm	462mm	Mild Steel	Galvanized	
CP2420	78570	564mm	462mm	Mild Steel	Powder Coated	White
CP2420G	26469	564mm	462mm	Mild Steel	Galvanized	
CP2424	78580	564mm	563mm	Mild Steel	Powder Coated	White
CP2424G	26479	564mm	563mm	Mild Steel	Galvanized	
CP3024	78610	716mm	563mm	Mild Steel	Powder Coated	White
CP3024G	26489	716mm	563mm	Mild Steel	Galvanized	
CP3624G	26579	869mm	563mm	Mild Steel	Galvanized	
CP3624	78650	869mm	563mm	Mild Steel	Powder Coated	White
CP3630	78660	869mm	716mm	Mild Steel	Powder Coated	White
CP3630G	26589	869mm	716mm	Mild Steel	Galvanized	
CP4230	78680	1021mm	716mm	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP4230G	15061	1021mm	716mm	Mild Steel	Galvanized	
CP4236	78690	1021mm	868mm	Mild Steel	Powder Coated	White
CP4236G	15062	1021mm	868mm	Mild Steel	Galvanized	
CP4836	78710	1173mm	868mm	Mild Steel	Powder Coated	White
CP4836G	15064	1173mm	868mm	Mild Steel	Galvanized	
CP6036G	15065	1478mm	868mm	Mild Steel	Galvanized	
CP6036	78720	1478mm	868mm	Mild Steel	Powder Coated	White
CP1212G	26429	259mm	259mm	Mild Steel	Galvanized	
CP1612	78520	361mm	259mm	Mild Steel	Powder Coated	White
CP1612G	26439	361mm	259mm	Mild Steel	Galvanized	
CP1616	78530	361mm	360mm	Mild Steel	Powder Coated	White
CP1616G	26449	361mm	360mm	Mild Steel	Galvanized	
CP2012	15634	462mm	259mm	Mild Steel	Powder Coated	White
CP2012G	15635	462mm	259mm	Mild Steel	Galvanized	
CP2014	15633	462mm	309mm	Mild Steel	Powder Coated	White
CP2014G	15636	462mm	309mm	Mild Steel	Galvanized	
CP2016	78540	462mm	360mm	Mild Steel	Powder Coated	White
CP2016G	26459	462mm	360mm	Mild Steel	Galvanized	
CP2412	29666	564mm	259mm	Mild Steel	Powder Coated	White
CP2412G	29667	564mm	259mm	Mild Steel	Galvanized	

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP2416	78560	564mm	360mm	Mild Steel	Powder Coated	White
CP2416G	15052	564mm	360mm	Mild Steel	Galvanized	
CP2442	78590	564mm	1021mm	Mild Steel	Powder Coated	White
CP2442G	15053	564mm	1021mm	Mild Steel	Galvanized	
CP3012	29668	716mm	259mm	Mild Steel	Powder Coated	White
CP3012G	29671	716mm	259mm	Mild Steel	Galvanized	
CP3016	29672	716mm	360mm	Mild Steel	Powder Coated	White
CP3016G	29673	716mm	360mm	Mild Steel	Galvanized	
CP3020	78600	716mm	462mm	Mild Steel	Powder Coated	White
CP3020G	15054	716mm	462mm	Mild Steel	Galvanized	
CP3030	78620	716mm	716mm	Mild Steel	Powder Coated	White
CP3030G	15055	716mm	716mm	Mild Steel	Galvanized	
CP3048	78630	716mm	1173mm	Mild Steel	Powder Coated	White
CP3048G	15056	716mm	1173mm	Mild Steel	Galvanized	
CP3060	78640	716mm	1478mm	Mild Steel	Powder Coated	White
CP3060G	15057	716mm	1478mm	Mild Steel	Galvanized	
CP3220	23782	767mm	462mm	Mild Steel	Powder Coated	White
CP3636	78670	869mm	868mm	Mild Steel	Powder Coated	White
CP3636G	15058	869mm	868mm	Mild Steel	Galvanized	
CP4242	29674	1021mm	1021mm	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP4242G	29675	1021mm	1021mm	Mild Steel	Galvanized	
CP4260	29676	1021mm	1478mm	Mild Steel	Powder Coated	White
CP4260G	29677	1021mm	1478mm	Mild Steel	Galvanized	
CP4420	23783	1072mm	462mm	Mild Steel	Powder Coated	White
CP4824	78700	1173mm	563mm	Mild Steel	Powder Coated	White
CP4824G	15063	1173mm	563mm	Mild Steel	Galvanized	
CP4848	29678	1173mm	1173mm	Mild Steel	Powder Coated	White
CP4848G	29681	1173mm	1173mm	Mild Steel	Galvanized	
CP5620	23784	1351mm	462mm	Mild Steel	Powder Coated	White
CP7230G	35272	1783mm	716mm	Mild Steel	Galvanized	
CP7236	15253	1783mm	868mm	Mild Steel	Powder Coated	White
CP7230	35271	1783mm	716mm	Mild Steel	Powder Coated	White

ADDITIONAL PRODUCT DETAILS

Catalog number CP4230 is used on Concept disconnect enclosures.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE