


Grid Straps



The Grid Straps are provided with specially designed rectangular holes to allow the use of cage nuts or front-loading cage nuts. Mounting holes are provided on 25-mm centers. Grid Straps are available with either 1 row or 3 rows of holes and are furnished in pairs. Mounting hardware to attach Grid Straps to the frame or to other Grid Straps is included.

FEATURES

Can be mounted vertically between horizontally mounted Grid Straps

Can be mounted left-to-right horizontally between front-to-back pairs or from the sides of the ProLine frame

Can be mounted front-to-back horizontally across the bottom or sides of the ProLine frame

When mounting width-wise from vertical to vertical, the grid strap chosen must be 100mm greater than the nominal size (i.e. 800mm wide enclosure would take a 900mm grid strap in this orientation)

Furnished in pairs, and constructed from 14 gauge (1.75mm) conductive steel

SPECIFICATIONS

Thickness: 1.9mm
Finish: Galvanized

Table 1/1

Catalog Number	Article Number	Material	Fits Frame Width	Fits Frame Depth	Hole Pattern	Quick Ship
PGH3S6	90560	Mild Steel		600mm	Three Rows	No
PGH1S6	90450	Mild Steel		600mm	One Row	No
PGH3S7	90570	Mild Steel	600mm	700mm	Three Rows	No
PGH1S7	90460	Mild Steel	600mm	700mm	One Row	No
PGH3S8	90580	Mild Steel	700mm	800mm	Three Rows	No
PGH1S8	90470	Mild Steel	700mm	800mm	One Row	No
PGH3S9	90590	Mild Steel	800mm	900mm	Three Rows	No
PGH3S5	90550	Mild Steel		500mm	Three Rows	No
PGH1S9	90480	Mild Steel	800mm	900mm	One Row	No
PGH1S5	90440	Mild Steel		500mm	One Row	No
PGH3S4	90540	Mild Steel		400mm	Three Rows	No
PGH1S11	90500	Mild Steel	1000mm		One Row	No
PGH3S11	90610	Mild Steel	1000mm	1100mm	Three Rows	No
PGH1S10	46869	Mild Steel	900mm	1000mm	One Row	No
PGH1S13	90520	Mild Steel	1200mm		One Row	No
PGH1S17	90530	Mild Steel	1600mm		One Row	No
PGH3S10	46879	Mild Steel	300mm	1000mm	Three Rows	No

Catalog Number	Article Number	Material	Fits Frame Width	Fits Frame Depth	Hole Pattern	Quick Ship
PGH3S12	16028	Mild Steel		1200mm	Three Rows	No
PGH3S13	90630	Mild Steel	1200mm		Three Rows	No
PGH3S17	90640	Mild Steel	1600mm		Three Rows	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE