

ProLine G2 Side Door Adapter



ProLine G2 Side Door Adapters allow the mounting of a standard door to the side of the enclosure. When mounted to the enclosure, they maintain enclosure environmental integrity.

FEATURES

All mounting hardware included

EMC versions are plated to provide corrosion resistance while maintaining a metal-to-metal contact

SPECIFICATIONS

Thickness: 1.9mm
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Quick Ship
P2DA105	31224	Mild Steel	No
P2DA106	31225	Mild Steel	No
P2DA108	31226	Mild Steel	No
P2DA125	31227	Mild Steel	No
P2DA126	31228	Mild Steel	No
P2DA128	31231	Mild Steel	No
P2DA145	31232	Mild Steel	No
P2DA146HF	31233	Mild Steel	No
P2DA148	31234	Mild Steel	No
P2DA164	31235	Mild Steel	No
P2DA165	31236	Mild Steel	No
P2DA166	31237	Mild Steel	No
P2DA168	31238	Mild Steel	No
P2DA184	31241	Mild Steel	No
P2DA185	31242	Mild Steel	No
P2DA186	31244	Mild Steel	No

Catalog Number	Article Number	Material	Quick Ship
P2DA186HF	31243	Mild Steel	No
P2DA188	31245	Mild Steel	No
P2DA2010	31246	Mild Steel	No
P2DA204	31247	Mild Steel	No
P2DA205	31248	Mild Steel	No
P2DA206	31253	Mild Steel	No
P2DA206HF	31252	Mild Steel	No
P2DA208	31254	Mild Steel	No
P2DA2210	31255	Mild Steel	No
P2DA225	31256	Mild Steel	No
P2DA226	31258	Mild Steel	No
P2DA226HF	31257	Mild Steel	No
P2DA228	31262	Mild Steel	No
P2DA64	31263	Mild Steel	No
P2DA66	31264	Mild Steel	No
P2DA68	31265	Mild Steel	No
P2DA86	31266	Mild Steel	No
P2DA88	31267	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE