

Panels for Free-Stand with Mounting Channel Two-Door



Panel for Free-Stand Single- and Dual-Access Two-Door Enclosures with Mounting Channel. Panels can be positioned anywhere along horizontal mounting channels (see Sections B-B for limitations). Half-length panels can be located in the upper or lower portion of the enclosure. Some assembly is required. Center support is furnished with each full-length or half-length panel for two-door enclosures. The center support attaches to the top and bottom mounting channels and can be positioned from front to back in the enclosure. The center support can be replaced with heavy duty panel supports to support panels when heavy equipment is installed.

FEATURES

Available in Full-Length and Half-Length

Plated mounting hardware is provided

SPECIFICATIONS

Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A60P48F1G	15022	1219mm	1117mm	Galvanized		3.04mm
A60P48F1	27610	1219mm	1117mm	Powder Coated	White	3.04mm
A72P48F2	27030	784mm	1117mm	Powder Coated	White	3.04mm
A72P48F2G	15013	784mm	1117mm	Galvanized		3.04mm
A72P48F1	27020	1524mm	1117mm	Powder Coated	White	3.04mm
A72P48F1G	15012	1524mm	1117mm	Galvanized		3.04mm
A90P48F2	27820	1013mm	1117mm	Powder Coated	White	3.04mm
A90P48F2G	15024	1013mm	1117mm	Galvanized		3.04mm
A72P60F1	27040	1524mm	1422mm	Powder Coated	White	3.04mm
A72P60F1G	15014	1524mm	1422mm	Galvanized		3.04mm
A72P60F2	27050	784mm	1422mm	Powder Coated	White	3.04mm
A72P60F2G	15015	784mm	1422mm	Galvanized		3.04mm
A72P72F1G	15016	1524mm	1727mm	Galvanized		3.04mm
A72P72F2G	15017	784mm	1727mm	Galvanized		3.04mm
A72P72F1	27060	1524mm	1727mm	Powder Coated	White	3.04mm
A72P72F2	27070	784mm	1727mm	Powder Coated	White	3.04mm
A90P72F2	27090	1013mm	1727mm	Powder Coated	White	3.04mm
A90P72F2G	15021	1013mm	1727mm	Galvanized		3.04mm

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A72P60F1B	57083	1524mm	1422mm	Powder Coated	White	3.04mm
A72P72F1B	57052	1524mm	1727mm	Powder Coated	White	3.04mm
A90P48F1	27810	1981mm	1117mm	Powder Coated	White	3.04mm
A90P48F1G	15023	1981mm	1117mm	Galvanized		3.04mm
A90P72F1G	15018	1981mm	1727mm	Galvanized		3.04mm
A90P72F1	27080	1981mm	1727mm	Powder Coated	White	3.04mm
A90PM72F1B	57037	1981mm	1727mm	Powder Coated	White	3.04mm

ADDITIONAL PRODUCT DETAILS

Catalog numbers with B suffix include two painted panels bolted together, with top and bottom stiffeners for additional support.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE