

ProLine Overlapping Doors



ProLine Overlapping Doors provide a door system for the full-width open front of 800,1000, 1200- and 1600-mm wide frames. The Primary door ensures a dust-tight seal using a 3-point roller latch system operated by a ProLine flush swing handle.

FEATURES

overlapping primary/adjacent door design allows unobstructed access

Furnished with a ProLine flush swing handle

Removable door bar is included on each door

Primary door is hinged on the right side

SPECIFICATIONS

Thickness: 1.9mm

Table 1/1

Catalog Number	Article Number	Material	Dimensions	Fits Frame	Color	Color Code
PTOD1212	29825	Mild Steel	1139 x 1191mm	1200 x 1200mm	Light Gray	RAL 7035
PTOD1412	29826	Mild Steel	1339 x 1191mm	1400 x 1200mm	Light Gray	RAL 7035
PTOD148	19764	Mild Steel	1339 x 792mm	1400 x 800mm	Light Gray	RAL 7035
PTOD1612	19775	Mild Steel	1539 x 1191mm	1600 x 1200mm	Light Gray	RAL 7035
PTOD168	19765	Mild Steel	1539 x 792mm	1600 x 800mm	Light Gray	RAL 7035
PTOD1810	19767	Mild Steel	1739 x 992mm	1800 x 1000mm	Light Gray	RAL 7035
PTOD1812	19776	Mild Steel	1739 x 1191mm	1800 x 1200mm	Light Gray	RAL 7035
PTOD1816	19783	Mild Steel	1739 x 1591mm	1800 x 1600mm	Light Gray	RAL 7035
PTOD1818	29827	Mild Steel	1739 x 1791mm	1800 x 1800mm	Light Gray	RAL 7035
PTOD188	19766	Mild Steel	1739 x 792mm	1800 x 800mm	Light Gray	RAL 7035
PTOD2010	19771	Mild Steel	1939 x 992mm	2000 x 1000mm	Light Gray	RAL 7035
PTOD2012	19777	Mild Steel	1939 x 1191mm	2000 x 1200mm	Light Gray	RAL 7035
PTOD2012SS	19778	Stainless Steel 304	1939 x 1191mm	2000 x 1200mm		
PTOD2016	19784	Mild Steel	1939 x 1591mm	2000 x 1600mm	Light Gray	RAL 7035
PTOD2018	29828	Mild Steel	1939 x 1891mm	2000 x 1800mm	Light Gray	RAL 7035
PTOD208	19768	Mild Steel	1939 x 792mm	2000 x 800mm	Light Gray	RAL 7035
PTOD2210	19773	Mild Steel	2139 x 992mm	2200 x 1000mm	Light Gray	RAL 7035
PTOD2212	19782	Mild Steel	2139 x 1191mm	2200 x 1200mm	Light Gray	RAL 7035

Catalog Number	Article Number	Material	Dimensions	Fits Frame	Color	Color Code
PTOD2212SS	19781	Stainless Steel 304	2139 x 1191mm	2200 x 1200mm		
PTOD228	19772	Mild Steel	2139 x 792mm	2200 x 800mm	Light Gray	RAL 7035
PTOD712	19774	Mild Steel	639 x 1191mm	700 x 1200mm	Light Gray	RAL 7035
PTOD78	19763	Mild Steel	639 x 792mm	700 x 800mm	Light Gray	RAL 7035

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE