

ProLine Solid Tops



Solid Tops are used to close the top opening on an enclosure frame. EMC Solid Tops are finished with paint over plated surfaces. Solid Tops are gasketed and include ground studs. Bolts are included to hold the top in place (lifting eyes can be used instead of bolts).

FEATURES

Solid Tops are finished with paint over plated surfaces

Solid Tops are gasketed and include ground studs

Bolts are included to hold the top in place (lifting eyes can be used instead of bolts)

SPECIFICATIONS

Thickness: 1.52mm

Table 1/1

Catalog Number	Article Number	Material	Finish	Color	Color Code	Fits Frame
PT66	96570	Mild Steel		Light Gray	RAL 7035	600 x 600mm
PT66SS	31809	Stainless Steel 304	Brushed			600 x 600mm
PT68SS	31819	Stainless Steel 304	Brushed			600 x 800mm
PT68	96580	Mild Steel		Light Gray	RAL 7035	600 x 800mm
PT85	96630	Mild Steel		Light Gray	RAL 7035	800 x 500mm
PT88SS	31839	Stainless Steel 304	Brushed			800 x 800mm
PT88	96650	Mild Steel		Light Gray	RAL 7035	800 x 800mm
PT64	96550	Mild Steel		Light Gray	RAL 7035	600 x 400mm
PT105	96670	Mild Steel		Light Gray	RAL 7035	1000 x 500mm
PT106SS	31849	Stainless Steel 304	Brushed			1000 x 600mm
PT106	96680	Mild Steel		Light Gray	RAL 7035	1000 x 600mm
PT108SS	31859	Stainless Steel 304	Brushed			1000 x 800mm
PT108	96690	Mild Steel		Light Gray	RAL 7035	1000 x 800mm
PT84	96620	Mild Steel		Light Gray	RAL 7035	800 x 400mm
PT86SS	31829	Stainless Steel 304	Brushed			800 x 600mm
PT86	96640	Mild Steel		Light Gray	RAL 7035	800 x 600mm
PT45	25459	Mild Steel		Light Gray	RAL 7035	400 x 500mm
PT46	25469	Mild Steel		Light Gray	RAL 7035	400 x 600mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Fits Frame
PT65	96560	Mild Steel		Light Gray	RAL 7035	600 x 500mm
PT76	96590	Mild Steel		Light Gray	RAL 7035	700 x 600mm
PT78	96600	Mild Steel		Light Gray	RAL 7035	700 x 800mm
PT89	96660	Mild Steel		Light Gray	RAL 7035	800 x 900mm
PT79	96610	Mild Steel		Light Gray	RAL 7035	700 x 900mm
PT104	29837	Mild Steel		Light Gray	RAL 7035	1000 x 400mm
PT105HF2	11999	Mild Steel		Light Gray	RAL 7035	1000 x 500mm
PT108HF2	12019	Mild Steel		Light Gray	RAL 7035	1000 x 800mm
PT124	96700	Mild Steel		Light Gray	RAL 7035	1200 x 400mm
PT125	96710	Mild Steel		Light Gray	RAL 7035	1200 x 500mm
PT126	96720	Mild Steel		Light Gray	RAL 7035	1200 x 600mm
PT126SS	31869	Stainless Steel 304	Brushed			1200 x 600mm
PT128	96730	Mild Steel		Light Gray	RAL 7035	1200 x 800mm
PT128SS	31879	Stainless Steel 304	Brushed			1200 x 800mm
PT164	29838	Mild Steel		Light Gray	RAL 7035	1600 x 400mm
PT165	96740	Mild Steel		Light Gray	RAL 7035	1600 x 500mm
PT166	96750	Mild Steel		Light Gray	RAL 7035	1600 x 600mm
PT168	96760	Mild Steel		Light Gray	RAL 7035	1600 x 800mm
PT185	25479	Mild Steel		Light Gray	RAL 7035	1800 x 500mm
PT186	25489	Mild Steel		Light Gray	RAL 7035	1800 x 600mm

Catalog Number	Article Number	Material	Finish	Color	Color Code	Fits Frame
PT188	29841	Mild Steel		Light Gray	RAL 7035	1800 x 800mm
PT64HF2	11879	Mild Steel		Light Gray	RAL 7035	600 x 400mm
PT66HF2	11899	Mild Steel		Light Gray	RAL 7035	600 x 600mm
PT68HF2	11909	Mild Steel		Light Gray	RAL 7035	600 x 800mm
PT78HF2	11929	Mild Steel		Light Gray	RAL 7035	700 x 800mm
PT79HF2	11939	Mild Steel		Light Gray	RAL 7035	700 x 900mm
PT84HF2	11949	Mild Steel		Light Gray	RAL 7035	800 x 400mm
PT86HF2	11969	Mild Steel		Light Gray	RAL 7035	800 x 600mm
PT88HF2	11979	Mild Steel		Light Gray	RAL 7035	800 x 800mm
PT89HF2	11989	Mild Steel		Light Gray	RAL 7035	800 x 900mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE