


# PropacPRO Trim Kit, Rear Side, for EMC Shielding



This kit can be used for covering the rear side and additionally shielding between the side panel and rear panels.

## CERTIFICATIONS



## FEATURES

For vertical EMC shielding between shielded front panels and side panel

## SPECIFICATIONS

|                        |               |
|------------------------|---------------|
| <b>Material:</b>       | Aluminum      |
| <b>Works With:</b>     | Cases         |
| <b>Finish:</b>         | Powder Coated |
| <b>Product Family:</b> | PropacPRO     |
| <b>Product Type:</b>   | Shielding Kit |

Table 1/1

| Catalog Number | Rack Height | Package Quantity | Height   | Quick Ship |
|----------------|-------------|------------------|----------|------------|
| 24576-018      | 2U          | 2                | 65.55mm  | No         |
| 24576-418      | 6U          | 2                | 243.35mm | No         |

| Catalog Number | Rack Height | Package Quantity | Height   | Quick Ship |
|----------------|-------------|------------------|----------|------------|
| 24576-218      | 4U          | 2                | 154.45mm | No         |
| 24576-118      | 3U          | 2                | 110mm    | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE