nVent SCHROFF

We connect and protect

Minipac Trapezoid Shape Case, Desktop

CATALOG NUMBER

24814-008





The Trapezoid Alu-profile case enables a user to insert 3 non standard PCBs. The PCBs will be inserted in grooves in the Alu-profile tube. Both sides are covered with 2.5 mm thick.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Desktop version
- PCB thickness 1.6 mm, spacing 15.24 mm (3 HP)
- Length D = 100 mm, width of long side 74.2 mm, width of short side 54.5 mm, height 46.1 mm
- Accommodates 3 non-standardized PCBs (height 50, 60 and 65 mm, depth 100 mm)

PRODUCT ATTRIBUTES

- Product Type: Small Form Factor Case
- Product Family: Minipac
- Type: Desktop
- Height: 75.6mm
- Width: 47.5mm
- Depth: 100.5mm

Material: Aluminum

Color: Black

Finish: Anodized

Protection Rating: IP40

Cooling: Non-Perforated

Shape: Trapezium

Package Quantity: 1

Length: 100.5mm

Net Weight: 0.24kg

ADDITIONAL PRODUCT DETAILS

Other dimensions on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.