

Galvanized Ground Rod, Pointed



CERTIFICATIONS



FEATURES

Meets ANSI®/NEMA® GR1

Zinc-coated exteriors are hot-dip galvanized for solid protection against corrosion, in accordance with ASTM® specification A123

Surfaces are rigidly inspected to eliminate seams, slivers and other defects

SPECIFICATIONS

Finish: Hot-Dip Galvanized

Material: Steel


Tensile Strength: 552 MPa Min

Table 1/1

Catalog Number	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Length (L)	Unit Weight	UPC Label	Certifications
811260UPC	1/2"	12.95 mm	1.8mm	1.8 kg	Yes	

CatalogNumber	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Length (L)	Unit Weight	UPC Label	Certifications
811280UPC	1/2"	12.95 mm	2.4mm	2.4 kg	Yes	
811350	1/2"	12.95 mm	1.52mm	1.5 kg	No	
811360	1/2"	12.95 mm	1.83mm	1.8 kg	No	
811380	1/2"	12.95 mm	2.44mm	2.4 kg	No	
815780	5/8"	14 mm	2.4mm	2.89 kg	No	UL
815800	5/8"	16 mm	3.05mm	4.8 kg	No	CSA, CSA-US
815800UPC	5/8"	16 mm	3mm	4.8 kg	Yes	
815850	5/8"	16 mm	1.52mm	2.4 kg	No	
815860	5/8"	16 mm	1.83mm	2.9 kg	No	
815860UPC	5/8"	16 mm	1.8mm	2.9 kg	Yes	
815880	5/8"	16 mm	2.44mm	3.8 kg	No	RUS
815880UPC	5/8"	16 mm	2.4mm	3.8 kg	Yes	RUS
813400	3/4"	18.54 mm	3.05mm	6.3 kg	No	UL
813400UPC	3/4"	18.54 mm	3mm	6.5 kg	Yes	UL
813480	3/4"	18.54 mm	2.44mm	5.1 kg	No	UL, RUS
814400	1"	25.65 mm	3.05mm	12.3 kg	No	CSA-US, CSA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE