

Door Panel for Concept HMI Enclosure



Use the door panel for mounting in the rear door of a Concept HMI enclosure.

FEATURES

Door panel is optional

Mounting hardware is included

SPECIFICATIONS

Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
CP2535	16758	132mm	232mm	Powder Coated	White	1.9mm
CP2535G	16761	132mm	232mm	Galvanized		1.9mm
CP3235	16764	207mm	232mm	Powder Coated	White	1.9mm
CP3040	16762	182mm	282mm	Powder Coated	White	1.9mm
CP3040G	16763	182mm	282mm	Galvanized		1.9mm
CP3235G	16765	207mm	232mm	Galvanized		1.9mm
CP3545	16766	232mm	332mm	Powder Coated	White	1.9mm
CP3545G	16767	232mm	332mm	Galvanized		1.9mm
CP3740	16768	257mm	282mm	Powder Coated	White	1.9mm
CP3740G	16771	257mm	282mm	Galvanized		1.9mm
CP4050	16772	282mm	382mm	Powder Coated	White	1.9mm
CP4050G	16773	282mm	382mm	Galvanized		1.9mm
CP4245	16774	307mm	332mm	Powder Coated	White	1.9mm
CP4245G	16775	307mm	332mm	Galvanized		1.9mm
CP4555	16776	331mm	432mm	Powder Coated	White	1.9mm
CP4555G	16777	331mm	432mm	Galvanized		1.9mm
CP4750	16778	357mm	382mm	Powder Coated	White	1.9mm
CP4750G	16781	357mm	382mm	Galvanized		1.9mm

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
CP4860	16782	361mm	482mm	Powder Coated	White	1.9mm
CP4860G	16783	361mm	482mm	Galvanized		1.9mm
CP5255	16784	407mm	432mm	Powder Coated	White	1.9mm
CP5255G	16785	407mm	432mm	Galvanized		1.9mm
CP5560	16786	437mm	482mm	Powder Coated	White	1.9mm
CP5560G	16787	437mm	482mm	Galvanized		1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE