

Hammer Die



FEATURES

Hardened steel die

Used to form the end of a field-made bond

Formed end designed to fit specific nVent ERICO Cadweld mold

SPECIFICATIONS

Material: Steel

Table 1/1

Catalog Number	Type	Conductor Size	nVent ERICO Sleeve
JD05	Grounding	1/0 Concentric	S05F
WD80	Power	1/0 Concentric	S05F
WD84	Power	2/0 Concentric, 1/0 Ropelay	S03F
JD03	Grounding	2/0 Concentric	S03F
JD06	Grounding	2/0 Ropelay	S06F
WD85	Power	2/0 Ropelay	S06F

Catalog Number	Type	Conductor Size	nVent ERICO Sleeve
SBD50	Signal	3/16" Bondstrand	SBS12C
JD01	Grounding	4/0 Concentric	S01F
WD82	Power	95 mm ² Concentric, 4/0 Concentric	S01F
JD02	Grounding	4/0 Ropelay	S02F
WD83	Power	4/0 Ropelay	S02F
WD88	Power	4/0 Welding cable	S429F3N16
SBD51	Signal	5/16" Bondstrand	SBS09C
SBD55	Signal	35 mm ² Concentric	S17F
WD94	Power	35 mm ² Concentric	S17F
PBWD102	Power	120 mm ² Concentric	H106F
PBWD104	Power	145 mm ² Concentric	S429F3N16
WD87	Power	150 mm ² Ropelay	S24F
PBWD106	Power	240 mm ² Concentric	S429FY922
WD105	Power	240 mm ² Concentric	S429FY922
PBWD99	Power	240 mm ² Ropelay	S429F3N16
JD07	Grounding	250 kcmil Ropelay	S07F
WD79	Power	500 kcmil Ropelay	S429F3S20
JD09	Grounding	#2 Concentric	S09F

Catalog Number	Type	Conductor Size	nVent ERICO Sleeve
JD11	Grounding	#4 Concentric	S20F

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE