

Panels for Free-Stand with Mounting Channel One-Door



Panel for Free-Stand Single- and Dual-Access One-Door Enclosures with Mounting Channel. Panels can be positioned anywhere along horizontal mounting channels (see dimension drawing Sections B-B for limitations). Half-length panels can be located in the upper or lower portion of the enclosure.

FEATURES

Available in Full-Length and Half-Length

Plated mounting hardware is provided

SPECIFICATIONS

Material: Mild Steel

Table 1/1						
Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A60P24F1G	14994	1219mm	508mm	Galvanized		2.66mm
A60P24F2G	14995	632mm	508mm	Galvanized		2.66mm
A60P24F1	21260	1219mm	508mm	Powder Coated	White	2.66mm
A60P24F2	21270	632mm	508mm	Powder Coated	White	2.66mm
A72P24F2	23330	784mm	508mm	Powder Coated	White	2.66mm
A72P24F2G	15001	784mm	508mm	Galvanized		2.66mm
A90P24F2	23510	1013mm	508mm	Powder Coated	White	2.66mm
A90P24F2G	15011	1013mm	508mm	Galvanized		2.66mm
A60P36F1G	14996	1219mm	812mm	Galvanized		2.66mm
A60P36F2G	14997	632mm	812mm	Galvanized		2.66mm
A60P36F1	21280	1219mm	812mm	Powder Coated	White	2.66mm
A60P36F2	21290	632mm	812mm	Powder Coated	White	2.66mm
A72P36F2	23370	784mm	812mm	Powder Coated	White	2.66mm
A90P36F2	23390	1013mm	812mm	Powder Coated	White	2.66mm
A72P36F2G	15005	784mm	812mm	Galvanized		2.66mm
A90P36F2G	15007	1013mm	812mm	Galvanized		2.66mm
A72P24F1	23320	1524mm	508mm	Powder Coated	White	2.66mm
A72P24F1G	14998	1524mm	508mm	Galvanized		2.66mm

Catalog Number	Article Number	Height	Width	Finish	Color	Thickness
A72P30F2G	15003	784mm	660mm	Galvanized		2.66mm
A72P30F1	23340	1524mm	660mm	Powder Coated	White	2.66mm
A72P30F2	23350	784mm	660mm	Powder Coated	White	2.66mm
A72P30F1G	15002	1524mm	660mm	Galvanized		2.66mm
A72P36F1G	15004	1524mm	812mm	Galvanized		2.66mm
A72P36F1	23360	1524mm	812mm	Powder Coated	White	2.66mm
A90P24F1G	15008	1981mm	508mm	Galvanized		2.66mm
A90P24F1	23480	1981mm	508mm	Powder Coated	White	2.66mm
A90P36F1G	15006	1981mm	812mm	Galvanized		2.66mm
A90P36F1	23380	1981mm	812mm	Powder Coated	White	2.66mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE