


RIM-CCB Cable Cover Bracket



nVent RAYCHEM Cable Cover Bracket is designed to mount on the roof or gutters and embeds one or two runs of self-regulating heating cable. It is used to enhance the heat transfer from the heating cable to the snow and create larger drain paths.

FEATURES

Long term roof de-icing solution by mechanically protecting the heating cable

Aesthetically pleasing solution by concealing the heating cable

High performance and reliable solution for snow melt in gutters or other roof sections

SPECIFICATIONS

Height:	8 mm
Width:	41 mm
Min Installation Temperature:	-18 °C

Table 1/1

Catalog Number	Item Name	Material	Color
R6201-AL-01		Aluminum	Slate Gray
R6201-AL-02		Aluminum	Stone White
R6201-AL-03	CCB-AL	Aluminum	Bone White
R6201-AL-04		Aluminum	Almond
R6201-AL-05		Aluminum	Sandstone

Catalog Number	Item Name	Material	Color
R6201-AL-06		Aluminum	Sierra Tan
R6201-AL-07		Aluminum	Teal
R6201-AL-08		Aluminum	Regal Blue
R6201-AL-09		Aluminum	Sky Blue
R6201-AL-10		Aluminum	Sherwood Green
R6201-AL-11		Aluminum	Hartford Green
R6201-AL-12		Aluminum	Hemlock Green
R6201-AL-13		Aluminum	Patina Green
R6201-AL-14		Aluminum	Dark Ivy
R6201-AL-15		Aluminum	Brandy Wine
R6201-AL-16		Aluminum	Regal Red
R6201-AL-17		Aluminum	Colonial Red
R6201-AL-18		Aluminum	Terra Cotta
R6201-AL-19		Aluminum	Dark Bronze
R6201-AL-20		Aluminum	Dark Bronze
R6201-AL-21		Aluminum	Mansard Brown
R6201-AL-22		Aluminum	Medium Bronze
R6201-AL-23	CCB-AL	Aluminum	Matte Black

Catalog Number	Item Name	Material	Color
R6201-AL-24		Aluminum	Classic Copper
R6201-AL-25		Aluminum	Silver Metallic
R6201-AL-26		Aluminum	Champagne
R6201-AL-27		Aluminum	Cityscape
R6201-AL-28		Aluminum	Charcoal Gray
R6201-AL-29		Aluminum	Tropical Patina
R6201-AL-30		Aluminum	Electric Blue
R6201-AL-31		Aluminum	Award Blue
R6201-AL-32		Aluminum	Granite Green
R6201-AL-50		Aluminum	
R6201-CU-70	CCB-CU	Copper	Copper

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT