

RIM-V Valley Panel



nVent RAYCHEM RIM-V valley panels are designed to mount in the roof valley to provide a heated melt path and prevent water ponding behind ice dams. Ideally used with the RIM-E eave panels, to ensure that snowmelt draining down the roof does not freeze and form ice dams in the lower portion of the valley.

FEATURES

Prevents ice dam problems in valleys, avoids consequential roof damage

An aesthetically attractive solution, with no visible cables, various colors and finishes

Simple to install and operate

Energy efficient, self-regulating heating cable plus advanced UL and CSA Certified control systems

Reliable during long life: 20 year product warranty available

Maintenance free

SPECIFICATIONS

Heating Capacity: 79 W/m

Cable Type: Self-Regulating

Table 1/1

Catalog Number	Nominal Voltage	Color
F6281-AL-01-1	120 V	Slate Gray
F6281-AL-01-2	240 V	Slate Gray
F6281-AL-02-1	120 V	Stone White
F6281-AL-02-2	240 V	Stone White

Catalog Number	Nominal Voltage	Color
F6281-AL-03-1	120 V	Bone White
F6281-AL-03-2	240 V	Bone White
F6281-AL-04-1	120 V	Almond
F6281-AL-04-2	240 V	Almond
F6281-AL-05-1	120 V	Sandstone
F6281-AL-05-2	240 V	Sandstone
F6281-AL-06-1	120 V	Sierra Tan
F6281-AL-06-2	240 V	Sierra Tan
F6281-AL-07-1	120 V	Teal
F6281-AL-07-2	240 V	Teal
F6281-AL-08-1	120 V	Regal Blue
F6281-AL-08-2	240 V	Regal Blue
F6281-AL-09-1	120 V	Sky Blue
F6281-AL-09-2	240 V	Sky Blue
F6281-AL-10-1	120 V	Sherwood Green
F6281-AL-10-2	240 V	Sherwood Green
F6281-AL-11-1	120 V	Hartford Green
F6281-AL-11-2	240 V	Hartford Green

Catalog Number	Nominal Voltage	Color
F6281-AL-12-1	120 V	Hemlock Green
F6281-AL-12-2	240 V	Hemlock Green
F6281-AL-13-1	120 V	Patina Green
F6281-AL-13-2	240 V	Patina Green
F6281-AL-14-1	120 V	Dark Ivy
F6281-AL-14-2	240 V	Dark Ivy
F6281-AL-15-1	120 V	Brandywine
F6281-AL-15-2	240 V	Brandywine
F6281-AL-16-1	120 V	Regal Red
F6281-AL-16-2	240 V	Regal Red
F6281-AL-17-1	120 V	Colonial Red
F6281-AL-17-2	240 V	Colonial Red
F6281-AL-18-1	120 V	Terra Cotta
F6281-AL-18-2	240 V	Terra Cotta
F6281-AL-19-1	120 V	Dark Bronze
F6281-AL-19-2	240 V	Dark Bronze
F6281-AL-20-1	120 V	Extra Dark Bronze
F6281-AL-20-2	240 V	Extra Dark Bronze

Catalog Number	Nominal Voltage	Color
F6281-AL-21-1	120 V	Mansard Brown
F6281-AL-21-2	240 V	Mansard Brown
F6281-AL-22-1	120 V	Medium Bronze
F6281-AL-22-2	240 V	Medium Bronze
F6281-AL-23-1	120 V	Matte Black
F6281-AL-23-2	240 V	Matte Black
F6281-AL-24-1	120 V	Classic Copper
F6281-AL-24-2	240 V	Classic Copper
F6281-AL-25-1	120 V	Silver Metallic
F6281-AL-25-2	240 V	Silver Metallic
F6281-AL-26-1	120 V	Champagne Metallic
F6281-AL-26-2	240 V	Champagne Metallic
F6281-AL-27-1	120 V	Cityscape
F6281-AL-27-2	240 V	Cityscape
F6281-AL-28-1	120 V	Charcoal Gray
F6281-AL-28-2	240 V	Charcoal Gray
F6281-AL-29-1	120 V	Tropical Patina
F6281-AL-29-2	240 V	Tropical Patina

Catalog Number	Nominal Voltage	Color
F6281-AL-30-1	120 V	Electric Blue
F6281-AL-30-2	240 V	Electric Blue
F6281-AL-31-1	120 V	Award Blue
F6281-AL-31-2	240 V	Award Blue
F6281-AL-32-1	120 V	Granite Green
F6281-AL-32-2	240 V	Granite Green
F6281-CU-70-1	120 V	Copper
F6281-CU-70-2	240 V	Copper

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT