


In-Pipe Retro Heating Cable



nVent RAYCHEM In-Pipe Retro is a pipe freeze protection system that heats uninsulated pipes from the inside. Utilizing a heavy-duty heating cable, it provides energy efficient in-pipe heating for pipes between 40 ft and 250 ft (12.2 m and 76.2 m) in length. Includes a ground-fault protected electronic controller. Designed for uninsulated 1" and 1-1/4" polyethylene pipes. Available in 120 V and 240 V options, with ground-fault protected electronic controller included.

FEATURES

Simple to design

Easy to install

Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIONS

Color:	Black
Sheath Material:	Copper
Outer Jacket Material:	Polyethylene
Ground Path Type:	Sheath

Table 1/1

Catalog Number	Item Name	Nominal Voltage
RWG40	RETRO-120-40	120 V
RWG41	RWG41	120 V
RWG42	RWG42	120 V
RWG43	RWG43	120 V
RWG44	RWG44	120 V

Catalog Number	Item Name	Nominal Voltage
RWG45	RWG45	120 V
RWG46	RWG46	120 V
RWG48	RWG48	120 V
RWG50	RETRO-120-50	120 V
RWG52	RWG52	120 V
RWG53	RWG53	120 V
RWG54	RWG54	120 V
RWG55	RWG55	120 V
RWG58	RWG58	120 V
RWG60	RETRO-120-60	120 V
RWG64	RWG64	120 V
RWG65	RWG65	120 V
RWG66	RWG66	120 V
RWG67	RWG67	120 V
RWG69	RWG69	120 V
RWG70	RETRO-120-70	120 V
RWG73	RWG73	120 V
RWG74	RWG74	120 V

Catalog Number	Item Name	Nominal Voltage
RWG75	RWG75	120 V
RWG76	RWG76	120 V
RWG80	RETRO-240-80	240 V
RWG801LV	RETRO-120-80	120 V
RWG831LV	RWG831LV	120 V
RWG84	RWG84	240 V
RWG841LV	RWG841LV	120 V
RWG85	RWG85	240 V
RWG851LV	RWG851LV	120 V
RWG86	RWG86	240 V
RWG861LV	RWG861LV	120 V
RWG88	RWG88	240 V
RWG881LV	RWG881LV	120 V
RWG90	RETRO-240-90	240 V
RWG901LV	RETRO-120-90	120 V
RWG92	RWG92	240 V
RWG921LV	RWG921LV	120 V
RWG93	RWG93	240 V

Catalog Number	Item Name	Nominal Voltage
RWG95	RWG95	240 V
RWG96	RWG96	240 V
RWG961LV	RWG961LV	120 V
RWG100	RETRO-240-100	240 V
RWG1001LV	RETRO-120-100	120 V
RWG1021LV	RWG1021LV	120 V
RWG105	RWG105	240 V
RWG110	RETRO-240-110	240 V
RWG1101LV	RETRO-120-110	120 V
RWG114	RWG114	240 V
RWG1151LV	RWG1151LV	120 V
RWG1201LV	RETRO-120-120	120 V
RWG1241LV	RWG1241LV	120 V
RWG1301LV	RETRO-120-130	120 V
RWG1351LV	RWG1351LV	120 V
RWG1401LV	RETRO-120-140	120 V
RWG1501LV	RETRO-120-150	120 V
RWG120	RETRO-240-120	240 V

Catalog Number	Item Name	Nominal Voltage
RWG122	RWG122	240 V
RWG125	RWG125	240 V
RWG127	RWG127	240 V
RWG130	RETRO-240-130	240 V
RWG135	RWG135	240 V
RWG136	RWG136	240 V
RWG140	RETRO-240-140	240 V
RWG150	RETRO-240-150	240 V
RWG155	RWG155	240 V
RWG157	RWG157	240 V
RWG160	RETRO-240-160	240 V
RWG165	RWG165	240 V
RWG168	RWG168	240 V
RWG170	RETRO-240-170	240 V
RWG172	RWG172	240 V
RWG175	RWG175	240 V
RWG176	RWG176	240 V
RWG180	RETRO-240-180	240 V

Catalog Number	Item Name	Nominal Voltage
RWG182	RWG182	240 V
RWG186	RWG186	240 V
RWG187	RWG187	240 V
RWG190	RETRO-240-190	240 V
RWG200	RETRO-240-200	240 V
RWG210	RETRO-240-210	240 V
RWG211	RWG211	240 V
RWG220	RETRO-240-220	240 V
RWG225	RWG225	240 V
RWG230	RETRO-240-230	240 V
RWG240	RETRO-240-240	240 V
RWG250	RETRO-240-250	240 V
RWG255	RWG255	240 V
RWG264	RWG264	240 V
RWG265	RWG265	240 V
RWG275	RWG275	240 V
RWG280	RWG280	240 V
RWG300	RWG300	240 V

Catalog Number	Item Name	Nominal Voltage
RWG310	RWG310	240 V
RWG350	RWG350	240 V
RWG360	RWG360	240 V
RWG370	RWG370	240 V
RWG375	RWG375	240 V
RWG380	RWG380	240 V
RWG390	RWG390	240 V
RWG400	RWG400	240 V
RWG420	RWG420	240 V
RWG455	RWG455	240 V
RWG460	RWG460	240 V
RWG500	RWG500	240 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT