

RIM-R Rake Panel



nVent RAYCHEM RIM-R rake panels are used on roof rakes to provide heated path for snow melt to the eave or gutter. RIM-R channel panels embed 2 runs of high wattage self-regulating cables and have a ledge on the cover panel to direct the snow melt flow.

FEATURES

Energy efficient, self-regulating heating cable plus advanced UL and CSA Certified control systems

Reliable during long life: 20 year product warranty available

Maintenance free

SPECIFICATIONS

Heating Capacity: 79 W/m
Cable Type: Self-Regulating

Table 1/1

Catalog Number	Nominal Voltage	Color
F6261-AL-01-1	120 V	Slate Gray
F6261-AL-01-2	240 V	Slate Gray
F6261-AL-02-1	120 V	Stone White
F6261-AL-02-2	240 V	Stone White
F6261-AL-03-1	120 V	Bone White
F6261-AL-03-2	240 V	Bone White

Catalog Number	Nominal Voltage	Color
F6261-AL-04-1	120 V	Almond
F6261-AL-04-2	240 V	Almond
F6261-AL-05-1	120 V	Sandstone
F6261-AL-05-2	240 V	Sandstone
F6261-AL-06-1	120 V	Sierra Tan
F6261-AL-06-2	240 V	Sierra Tan
F6261-AL-07-1	120 V	Teal
F6261-AL-07-2	240 V	Teal
F6261-AL-08-1	120 V	Regal Blue
F6261-AL-08-2	240 V	Regal Blue
F6261-AL-09-1	120 V	Sky Blue
F6261-AL-09-2	240 V	Sky Blue
F6261-AL-10-1	120 V	Sherwood Green
F6261-AL-10-2	240 V	Sherwood Green
F6261-AL-11-1	120 V	Hartford Green
F6261-AL-11-2	240 V	Hartford Green
F6261-AL-12-1	120 V	Hemlock Green
F6261-AL-12-2	240 V	Hemlock Green

Catalog Number	Nominal Voltage	Color
F6261-AL-13-1	120 V	Patina Green
F6261-AL-13-2	240 V	Patina Green
F6261-AL-14-1	120 V	Dark Ivy
F6261-AL-14-2	240 V	Dark Ivy
F6261-AL-15-1	120 V	Brandywine
F6261-AL-15-2	240 V	Brandywine
F6261-AL-16-1	120 V	Regal Red
F6261-AL-16-2	240 V	Regal Red
F6261-AL-17-1	120 V	Colonial Red
F6261-AL-17-2	240 V	Colonial Red
F6261-AL-18-1	120 V	Terra Cotta
F6261-AL-18-2	240 V	Terra Cotta
F6261-AL-19-1	120 V	Dark Bronze
F6261-AL-19-2	240 V	Dark Bronze
F6261-AL-20-1	120 V	Extra Dark Bronze
F6261-AL-20-2	240 V	Extra Dark Bronze
F6261-AL-21-1	120 V	Mansard Brown
F6261-AL-21-2	240 V	Mansard Brown

Catalog Number	Nominal Voltage	Color
F6261-AL-22-1	120 V	Medium Bronze
F6261-AL-22-2	240 V	Medium Bronze
F6261-AL-23-1	120 V	Matte Black
F6261-AL-23-2	240 V	Matte Black
F6261-AL-24-1	120 V	Classic Copper
F6261-AL-24-2	240 V	Classic Copper
F6261-AL-25-1	120 V	Silver Metallic
F6261-AL-25-2	240 V	Silver Metallic
F6261-AL-26-1	120 V	Champagne Metallic
F6261-AL-26-2	240 V	Champagne Metallic
F6261-AL-27-1	120 V	Cityscape
F6261-AL-27-2	240 V	Cityscape
F6261-AL-28-1	120 V	Charcoal Gray
F6261-AL-28-2	240 V	Charcoal Gray
F6261-AL-29-1	120 V	Tropical Patina
F6261-AL-29-2	240 V	Tropical Patina
F6261-AL-30-1	120 V	Electric Blue
F6261-AL-30-2	240 V	Electric Blue

Catalog Number	Nominal Voltage	Color
F6261-AL-31-1	120 V	Award Blue
F6261-AL-31-2	240 V	Award Blue
F6261-AL-32-1	120 V	Granite Green
F6261-AL-32-2	240 V	Granite Green
F6261-CU-70-1	120 V	Copper
F6261-CU-70-2	240 V	Copper

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT