

PMC Mezzanine Front Panel, Non-Shielded



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments.

CERTIFICATIONS



FEATURES

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Accessory Type	Mounting	EMC Shielding	Gasket Type	Material
20835-899	Mezzanine Front Panel	Front panel	Snapped in	No (Retrofittable)	O-Ring EMC	Aluminum
20835-896	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc
20835-931	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc
20835-929	Front Panel without Handle		Screw-on Front	No (Retrofittable)		Zinc

Table 2/3

Catalog Number	Front Finish	Rear Finish	Treated Edges	Height	Width	Complies With
20835-899	Anodized	Conductive	Yes	74mm	12.7mm	PMC Mezzanine, IEEE P1386
20835-896	Anodized	Anodized	No	74mm	12.7mm	PMC Mezzanine, IEEE P1386
20835-931	Anodized	Conductive	No	74mm	12.7mm	PMC Mezzanine, IEEE P1386
20835-929	Chrome Plated	Chrome Plated	Yes	74mm	12.7mm	PMC Mezzanine, IEEE P1386

Table 3/3

Catalog Number	Depth	Package Quantity	Finish	Quick Ship
20835-899	2.5mm	10	Anodized	No
20835-896		10		No
20835-931		10		No
20835-929		10		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE