

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



FEATURES

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFICATIONS

Product Type: Assembly Kit

Finish: Zinc Plated

Table 1/2

Catalog Number	Length	Package Quantity	Thread Size	Material	Product Family	Type
----------------	--------	------------------	-------------	----------	----------------	------

21190-095		4	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit
21120-196	16mm	4	M6	Steel		Mounting Kit, Grounding
21100-435		8	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-215		32	M6	Steel		Mounting Kit
21101-809		50	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-214		50	M6	Steel		Mounting Kit
21120-198	16mm	50	M6	Steel		Mounting Kit, Grounding

21101-810		100	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-216		100	M6	Steel		Mounting Kit
21120-213		4	M6	Steel		Mounting Kit
21120-199	13mm	100	M6	Steel		Mounting Kit, Grounding
21120-197	16mm	32	M6	Steel		Mounting Kit, Grounding
21190-435		32	M6	Steel, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit

Table 2/2

Catalog Number	Works With	Certifications	Quick Ship
21190-095	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	No
21120-196	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21100-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	No
21120-215	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No

Catalog Number	Works With	Certifications	Quick Ship
21101-809	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	No
21120-214	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21120-198	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21101-810	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	No
21120-216	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21120-213	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21120-199	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21120-197	Front Panels, Eurorack, Novastar, Varistar, Varistar CP		No
21190-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE