


Novastar Glazed Acrylic Glass Door



Glazed / Glass doors for aluminum frame cabinets with attractive design, ideally suited for general electronics, test & measurement, audio/video and broadcasting applications.

CERTIFICATIONS



FEATURES

Mounting front or rear

Opening angle 180°

Lock with key

SPECIFICATIONS

Product Type: Cabinet Door

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Package Quantity	Color	Color Code
25230-092	6U	322mm	553mm	1	Black Grey	RAL 7021
25230-093	9U	456mm	553mm	1	Black Grey	RAL 7021
25230-094	12U	589mm	553mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Package Quantity	Color	Color Code
25230-095	16U	767mm	553mm	1	Black Grey	RAL 7021
25230-096	20U	945mm	553mm	1	Black Grey	RAL 7021
25230-097	25U	1167mm	553mm	1	Black Grey	RAL 7021
25230-098	34U	1567mm	553mm	1	Black Grey	RAL 7021
25230-099	38U	1745mm	533mm	1	Black Grey	RAL 7021
25230-100	43U	1967mm	533mm	1	Black Grey	RAL 7021
25230-101	47U	2145mm	553mm	1	Black Grey	RAL 7021
25230-102	29U	1345mm	553mm	1	Black Grey	RAL 7021
26230-092	6U	322mm	553mm	1	Light Grey	RAL 7035
26230-093	9U	456mm	553mm	1	Light Grey	RAL 7035
26230-094	12U	589mm	533mm	1	Light Grey	RAL 7035
26230-095	16U	767mm	533mm	1	Light Grey	RAL 7035
26230-096	20U	945mm	553mm	1	Light Grey	RAL 7035
26230-097	25U	1167mm	553mm	1	Light Grey	RAL 7035
26230-098	34U	1567mm	553mm	1	Light Grey	RAL 7035
26230-099	38U	1745mm	553mm	1	Light Grey	RAL 7035
26230-100	43U	1967mm	553mm	1	Light Grey	RAL 7035
26230-101	47U	2145mm	553mm	1	Light Grey	RAL 7035

CatalogNumber	Rack Height	Height	Width	Package Quantity	Color	Color Code
26230-102	29U	1345mm	553mm	1	Light Grey	RAL 7035

Table 2/2

Catalog Number	Finish	Type	Quick Ship
25230-092	Powder Coated	Glass Door	No
25230-093	Powder Coated	Glass Door	No
25230-094	Powder Coated	Glass Door	No
25230-095	Powder Coated	Glass Door	No
25230-096	Powder Coated	Glass Door	No
25230-097	Powder Coated	Glass Door	No
25230-098	Powder Coated	Glass Door	No
25230-099	Powder Coated	Glass Door	No
25230-100	Powder Coated	Glass Door	No
25230-101	Powder Coated	Glass Door	No
25230-102	Powder Coated	Glass Door	No
26230-092	Powder Coated	Glass Door	No
26230-093	Powder Coated	Glass Door	No
26230-094	Powder Coated	Glass Door	No
26230-095	Powder Coated	Glass Door	No
26230-096	Powder Coated	Glass Door	No

Catalog Number	Finish	Type	Quick Ship
26230-097	Powder Coated	Glass Door	No
26230-098	Powder Coated	Glass Door	No
26230-099	Powder Coated	Glass Door	No
26230-100	Powder Coated	Glass Door	No
26230-101	Powder Coated	Glass Door	No
26230-102	Powder Coated	Glass Door	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE