

# MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

## Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

## CERTIFICATIONS



## FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Depth  | Usable Width | Mounting | Complies With                    | EMC Shielding      |
|----------------|-------------|--------|--------------|----------|----------------------------------|--------------------|
| 20860-621      | 1 U         | 220 mm | 403 mm       | Rack     | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-622      | 1 U         | 280 mm | 403 mm       | Rack     | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-625      | 2 U         | 280 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-626      | 2 U         | 340 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-627      | 3 U         | 280 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-628      | 3 U         | 340 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-629      | 3 U         | 400 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-632      | 4 U         | 340 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-633      | 4 U         | 400 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-634      | 4 U         | 460 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-635      | 5 U         | 460 mm | 403 mm       | Rack     | IEC 60297-3-100                  | No (Retrofittable) |

Table 2/2

| Catalog Number | Product Family | Product Type    | Type       |
|----------------|----------------|-----------------|------------|
| 20860-621      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-622      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-625      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-626      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-627      | MultipacPRO    | Subrack/Chassis | Perforated |

| Catalog Number | Product Family | Product Type    | Type       |
|----------------|----------------|-----------------|------------|
| 20860-628      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-629      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-632      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-633      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-634      | MultipacPRO    | Subrack/Chassis | Perforated |
| 20860-635      | MultipacPRO    | Subrack/Chassis | Perforated |

### ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE