



# Frame Type Plug-In Unit Cover Plate, Without Perforation, 12 HP, 227 mm

## CATALOG NUMBER

**34813-412**



| HP | W      |
|----|--------|
| 8  | 5,08   |
| 10 | 15,24  |
| 12 | 25,40  |
| 14 | 35,56  |
| 21 | 71,12  |
| 28 | 106,68 |
| 42 | 177,80 |



Cover plate for frame-type plug-in units, plain.

## CERTIFICATIONS



## FEATURES

Cover plate is inserted top and bottom between the side Panels

PCB only possible in slot 1

## PRODUCT ATTRIBUTES

Rack Width: 12HP

Depth (D): 227mm

Package Quantity: 1

Finish: Zinc Plated

Length (L): 220mm

Material: Steel

Product Type: Cover

Type: screw-fixed


Works With: Cassettes

Net Weight: 0.062kg

## ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE