





Extractor Handle Trapezoid Form, Type 1, Top, Grey

CATALOG NUMBER

20817-328



Extractor handle trapezoid form 1 can be used to extract PCBs. The handle must be assembled into the slot of the front panel.

CERTIFICATIONS



FEATURES

Handle closed laterally, PC, UL 94 V-0

Pivot bush

Identification plate, Al, 1.5 mm, anodized, cut edges plain

Board support die-cast zinc

In the 6U version, space can be created for SMD components on the left side by swapping the top and bottom handles and thus moving the PCB position 1 HP to the right

PRODUCT ATTRIBUTES

Color: Light Grey

Package Quantity: 1

Handle Type: Trapezoid, Type 1

Flammability Rating: UL® 94V-0

Color Code: RAL 7035

Complies With: EN 45545-2, R22-R24, HL3; IEC 60297-3-101

Depth: 26.3mm

Height: 17.8mm

Material: Polycarbonate

Product Type: Handle

Type: Extractor

Works With: Front Panels

Gross Weight: 0.009kg

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE