

# Ventilation Roofs, CVR

The ventilation roof plate provides cost effective natural ventilation while keeping insects and dust out.



## FEATURES

---

Description: Raised roof with 2.5 mm ventilation slots and filter material.

Material: 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

Finish: RAL 7035 structured powder coating.

Temperature resistance: 100 °C.

Protection: Complies with IP 31, TYPE 1.

Pack quantity: 1 piece with mounting brackets and ventilation filter.

Note: Increases the enclosure height by 40 mm.

SPECIFICATIONS

**Thickness:** 1.5mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |                |        |        |       |                |                    |
|----------------|----------------|--------|--------|-------|----------------|--------------------|
| Catalog Number | Article Number | Height | Width  | Depth | Product Family | Enclosure Material |
| CVR0505R5      | CVR0505R5      | 58mm   | 500mm  | 500mm | Free-Standing  | Mild Steel         |
| CVR0603R5      | CVR0603R5      | 58mm   | 600mm  | 300mm | Free-Standing  | Mild Steel         |
| CVR0604R5      | CVR0604R5      | 58mm   | 600mm  | 400mm | Free-Standing  | Mild Steel         |
| CVR0605R5      | CVR0605R5      | 58mm   | 600mm  | 500mm | Free-Standing  | Mild Steel         |
| CVR0606R5      | CVR0606R5      | 58mm   | 600mm  | 600mm | Free-Standing  | Mild Steel         |
| CVR0608R5      | CVR0608R5      | 58mm   | 600mm  | 800mm | Free-Standing  | Mild Steel         |
| CVR0803R5      | CVR0803R5      | 58mm   | 800mm  | 300mm | Free-Standing  | Mild Steel         |
| CVR0804R5      | CVR0804R5      | 58mm   | 800mm  | 400mm | Free-Standing  | Mild Steel         |
| CVR0805R5      | CVR0805R5      | 58mm   | 800mm  | 500mm | Free-Standing  | Mild Steel         |
| CVR0806R5      | CVR0806R5      | 58mm   | 800mm  | 600mm | Free-Standing  | Mild Steel         |
| CVR0808R5      | CVR0808R5      | 58mm   | 800mm  | 800mm | Free-Standing  | Mild Steel         |
| CVR0809R5      | CVR0809R5      | 58mm   | 800mm  | 900mm | Free-Standing  | Mild Steel         |
| CVR1003R5      | CVR1003R5      | 58mm   | 1000mm | 300mm | Free-Standing  | Mild Steel         |
| CVR1004R5      | CVR1004R5      | 58mm   | 1000mm | 400mm | Free-Standing  | Mild Steel         |
| CVR1005R5      | CVR1005R5      | 58mm   | 1000mm | 500mm | Free-Standing  | Mild Steel         |
| CVR1006R5      | CVR1006R5      | 58mm   | 1000mm | 600mm | Free-Standing  | Mild Steel         |

| Catalog Number | Article Number | Height | Width  | Depth | Product Family | EnclosureMaterial |
|----------------|----------------|--------|--------|-------|----------------|-------------------|
| CVR1008R5      | CVR1008R5      | 58mm   | 1000mm | 800mm | Free-Standing  | Mild Steel        |
| CVR1203R5      | CVR1203R5      | 58mm   | 1200mm | 300mm | Free-Standing  | Mild Steel        |
| CVR1204R5      | CVR1204R5      | 58mm   | 1200mm | 400mm | Free-Standing  | Mild Steel        |
| CVR1205R5      | CVR1205R5      | 58mm   | 1200mm | 500mm | Free-Standing  | Mild Steel        |
| CVR1206R5      | CVR1206R5      | 58mm   | 1200mm | 600mm | Free-Standing  | Mild Steel        |
| CVR1208R5      | CVR1208R5      | 58mm   | 1200mm | 800mm | Free-Standing  | Mild Steel        |
| CVR1604R5      | CVR1604R5      | 58mm   | 1600mm | 400mm | Free-Standing  | Mild Steel        |
| CVR1605R5      | CVR1605R5      | 58mm   | 1600mm | 500mm | Free-Standing  | Mild Steel        |
| CVR1606R5      | CVR1606R5      | 58mm   | 1600mm | 600mm | Free-Standing  | Mild Steel        |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**