

Novastar Side Panel for Slim-Line

Power Utilities



Steel Side Panels for Slim.Line aluminum frame with quick fastener for easy mounting and installation. Schroff delivers cladding parts with grounding cable installed and tested

CERTIFICATIONS



FEATURES

Side panel with quarter-turn fastener, includes grounding

St, 1 mm

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Depth	Color	Color Code	Product Type
25230-070	6 U	357 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

CatalogNumber	Rack Height	Height	Depth	Color	Color Code	Product Type
25230-120	6 U	357 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-070	6 U	357 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-120	6 U	357 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-071	9 U	490 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-121	9 U	490 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-071	9 U	490 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-121	9 U	490 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-072	12 U	589 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-113	12 U	531 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-114	12 U	531 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-122	12 U	589 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-172	12 U	589 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-072	12 U	589 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-113	12 U	531 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-114	12 U	531 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-122	12 U	589 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-172	12 U	589 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-073	16 U	709 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

CatalogNumber	Rack Height	Height	Depth	Color	Color Code	Product Type
25230-115	16 U	709 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-116	16 U	709 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-123	16 U	709 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-173	16 U	709 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-073	16 U	709 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-115	16 U	709 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-116	16 U	709 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-123	16 U	709 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-173	16 U	709 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-074	20 U	945 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-117	20 U	887 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-118	20 U	887 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-124	20 U	945 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-174	20 U	945 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-074	20 U	945 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-117	20 U	887 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-118	20 U	887 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-124	20 U	945 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

CatalogNumber	Rack Height	Height	Depth	Color	Color Code	Product Type
26230-174	20 U	945 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-075	25 U	1167 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-119	25 U	1109 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-125	25 U	1167 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-130	25 U	1109 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-175	25 U	1167 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-075	25 U	1167 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-119	25 U	1109 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-125	25 U	1167 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-130	25 U	1109 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-175	25 U	1167 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-076	34 U	1567 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-126	34 U	1567 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-131	34 U	1509 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-132	34 U	1509 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-176	34 U	1567 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-076	34 U	1567 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-126	34 U	1567 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

CatalogNumber	Rack Height	Height	Depth	Color	Color Code	Product Type
26230-131	34 U	1509 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-132	34 U	1509 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-176	34 U	1567 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-077	38 U	1745 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-127	38 U	1745 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-133	38 U	1687 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-134	38 U	1687 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-177	38 U	1745 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-077	38 U	1745 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-127	38 U	1745 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-133	38 U	1687 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-134	38 U	1687 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-177	38 U	1745 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-078	43 U	1967 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-128	43 U	1967 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-135	43 U	1909 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-136	43 U	1909 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-178	43 U	1967 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

CatalogNumber	Rack Height	Height	Depth	Color	Color Code	Product Type
26230-078	43 U	1967 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-128	43 U	1967 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-135	43 U	1909 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-136	43 U	1909 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-178	43 U	1967 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-079	47 U	2145 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-129	47 U	2145 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-137	47 U	2087 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-138	47 U	2087 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-179	47 U	2145 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-079	47 U	2145 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-129	47 U	2145 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-137	47 U	2087 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-138	47 U	2087 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-179	47 U	2145 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Table 2/2

Catalog Number	Type
25230-070	Side Panel
25230-120	Side Panel

Catalog Number	Type
26230-070	Side Panel
26230-120	Side Panel
25230-071	Side Panel
25230-121	Side Panel
26230-071	Side Panel
26230-121	Side Panel
25230-072	Side Panel
25230-113	Side Panel
25230-114	Side Panel
25230-122	Side Panel
25230-172	Side Panel
26230-072	Side Panel
26230-113	Side Panel
26230-114	Side Panel
26230-122	Side Panel
26230-172	Side Panel
25230-073	Side Panel
25230-115	Side Panel

Catalog Number	Type
25230-116	Side Panel
25230-123	Side Panel
25230-173	Side Panel
26230-073	Side Panel
26230-115	Side Panel
26230-116	Side Panel
26230-123	Side Panel
26230-173	Side Panel
25230-074	Side Panel
25230-117	Side Panel
25230-118	Side Panel
25230-124	Side Panel
25230-174	Side Panel
26230-074	Side Panel
26230-117	Side Panel
26230-118	Side Panel
26230-124	Side Panel
26230-174	Side Panel

Catalog Number	Type
25230-075	Side Panel
25230-119	Side Panel
25230-125	Side Panel
25230-130	Side Panel
25230-175	Side Panel
26230-075	Side Panel
26230-119	Side Panel
26230-125	Side Panel
26230-130	Side Panel
26230-175	Side Panel
25230-076	Side Panel
25230-126	Side Panel
25230-131	Side Panel
25230-132	Side Panel
25230-176	Side Panel
26230-076	Side Panel
26230-126	Side Panel
26230-131	Side Panel

Catalog Number	Type
26230-132	Side Panel
26230-176	Side Panel
25230-077	Side Panel
25230-127	Side Panel
25230-133	Side Panel
25230-134	Side Panel
25230-177	Side Panel
26230-077	Side Panel
26230-127	Side Panel
26230-133	Side Panel
26230-134	Side Panel
26230-177	Side Panel
25230-078	Side Panel
25230-128	Side Panel
25230-135	Side Panel
25230-136	Side Panel
25230-178	Side Panel
26230-078	Side Panel

Catalog Number	Type
26230-128	Side Panel
26230-135	Side Panel
26230-136	Side Panel
26230-178	Side Panel
25230-079	Side Panel
25230-129	Side Panel
25230-137	Side Panel
25230-138	Side Panel
25230-179	Side Panel
26230-079	Side Panel
26230-129	Side Panel
26230-137	Side Panel
26230-138	Side Panel
26230-179	Side Panel

ADDITIONAL PRODUCT DETAILS

Optionally the quarter-turn fastener can be fitted with a side panel lock.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE