

Telescopic Slide Universal, Slim, 2 U

Slim Universal Telescopic Slide, 2 U.



CERTIFICATIONS



FEATURES

Rail width k = 9.7 mm, max. installation width of extension/drawer w = 429 mm

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

Locking at full extension

Static load-carrying capacity per pair 46 - 57 kg

Extension length > 110 %

SPECIFICATIONS

Material: Steel

Product Type: Telescopic Slide
Finish: Zinc Plated

Table 1/1							
Catalog Number	Length	Package Quantity	Static Load	Туре	Quick Ship		
20110-071	356mm	2	57kg	Universal	No		

Catalog Number	Length	Package Quantity	Static Load	Туре	Quick Ship
20110-077	610mm	2	46kg	Universal	No
20110-076	584mm	2	46kg	Universal	No
20110-075	559mm	2	46kg	Universal	No
20110-074	508mm	2	55kg	Universal	No
20110-072	406mm	2	55kg	Universal	No
20110-073	457mm	2	55kg	Universal	No

ADDITIONAL PRODUCT DETAILS

Universal telescopic Rails can also be fitted without additional components in non-standard applications, this also in other than 19" cabinets.

To mount on 19" plane please order assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE