

# Varistar CP Flat Top Cover With Cutouts

Rack top cover with cut out zones. Brushes, edge protection or cover panle have to chosen form the accessory range.

Flat top cover with cutout + brush strip\_Varistar CP

## FEATURES

Flat top cover with cutouts

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Top Cover

**Color Code:** RAL 7021

**Material:** Steel

Table 1/2

| Catalog Number | Width | Depth  | Package Quantity | Color      | Finish        | Type   |
|----------------|-------|--------|------------------|------------|---------------|--------|
| 21630-034      | 600mm | 1000mm | 1                | Black Grey | Powder Coated | Cutout |
| 21630-042      | 800mm | 1200mm | 1                | Black Grey | Powder Coated | Cutout |
| 21630-041      | 800mm | 1100mm | 1                | Black Grey | Powder Coated | Cutout |
| 21630-040      | 800mm | 1000mm | 1                | Black Grey | Powder Coated | Cutout |
| 21630-036      | 600mm | 1200mm | 1                | Black Grey | Powder Coated | Cutout |
| 21630-035      | 600mm | 1100mm | 1                | Black Grey | Powder Coated | Cutout |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 21630-034      | No         |

| Catalog Number | Quick Ship |
|----------------|------------|
| 21630-042      | No         |
| 21630-041      | No         |
| 21630-040      | No         |
| 21630-036      | No         |
| 21630-035      | No         |

## ADDITIONAL PRODUCT DETAILS

Please order brushes, cover panels from the accessory range.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**