

# CleanTray 90-Degree Tee



Clean Tray 90-Degree Tees are used for right-angle installations where two 90-degree transitions are required. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

## FEATURES

---

Clean Tray 90-Degree Tees are used for right-angle installations where two 90-degree transitions are required

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

## SPECIFICATIONS

**Finish:** Brushed #3  
**Material:** Stainless Steel 304

Table 1/1

| Catalog Number | Type | Height | Width | Thickness | Quick Ship |
|----------------|------|--------|-------|-----------|------------|
| CT22TFCSS      | Tee  | 51mm   | 51mm  | 1.27mm    | No         |
| CT33TFCSS      | Tee  | 76mm   | 76mm  | 1.27mm    | No         |
| CT33TICSS      | Tee  | 76mm   | 76mm  | 1.27mm    | No         |
| CT33TOCSS      | Tee  | 76mm   | 76mm  | 1.27mm    | No         |
| CT44PTFCSS     | Tee  | 102mm  | 102mm | 1.27mm    | No         |
| CT44TFCSS      | Tee  | 102mm  | 102mm | 1.27mm    | No         |
| CT44TICSS      | Tee  | 102mm  | 102mm | 1.27mm    | No         |
| CT44TOCSS      | Tee  | 102mm  | 102mm | 1.27mm    | No         |
| CT46TFCSS      | Tee  | 102mm  | 152mm | 1.27mm    | No         |
| CT46TICSS      | Tee  | 102mm  | 152mm | 1.27mm    | No         |
| CT46TOCSS      | Tee  | 102mm  | 152mm | 1.27mm    | No         |
| CT66TFCSS      | Tee  | 152mm  | 152mm | 1.27mm    | No         |
| CT66TICSS      | Tee  | 152mm  | 152mm | 1.27mm    | No         |
| CT66TOCSS      | Tee  | 152mm  | 152mm | 1.27mm    | No         |
| CTS33PTFCSS    | Tee  | 76mm   | 76mm  | 1.27mm    | No         |
| CTS33TFCSS     | Tee  | 76mm   | 76mm  | 1.27mm    | No         |
| CTS44PTFCSS    | Tee  | 102mm  | 102mm | 1.27mm    | No         |

| Catalog Number | Type | Height | Width | Thickness | Quick Ship |
|----------------|------|--------|-------|-----------|------------|
| CTS44TFCSS     | Tee  | 102mm  | 102mm | 1.27mm    | No         |
| CTS46PTFCSS    | Tee  | 102mm  | 152mm | 1.27mm    | No         |
| CTS46TFCSS     | Tee  | 102mm  | 152mm | 1.27mm    | No         |
| CTS66PTFCSS    | Tee  | 152mm  | 152mm | 1.27mm    | No         |
| CTS66TFCSS     | Tee  | 152mm  | 152mm | 1.27mm    | No         |
| CT22PTFCSS     | Tee  | 51mm   | 51mm  | 1.27mm    | No         |
| CT22TOCSS      | Tee  | 51mm   | 51mm  | 1.27mm    | No         |
| CT33PTFCSS     | Tee  | 76mm   | 76mm  | 1.27mm    | No         |
| CT46PTFCSS     | Tee  | 102mm  | 152mm | 1.27mm    | No         |
| CT66PTFCSS     | Tee  | 152mm  | 152mm | 1.27mm    | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**