

Standard Termination Kit



nVent PYROTENAX Standard Termination Kit are a range of standard screw on termination kits to install plain seals (RPS) on light or heavy duty mineral insulated (MI) cables. Available in various sizes, with a continuous operating temperature range up to 105 °C. Suitable for the majority of general wiring applications.

FEATURES

- Simple to install
- Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Max Operating Temperature:	105 °C
Voltage Rating:	500 – 750 V

Catalog Number
RPS12H1.532
RPS12H2.532
RPS19H1.540
RPS1H1020
RPS1H12032
RPS1H15032
RPS1H1620

Catalog Number
RPS1H18532
RPS1H2.520
RPS1H24040
RPS1H2520
RPS1H3520
RPS1H5025
RPS1H620
RPS1H7025
RPS1H9525
RPS2H1.520
RPS2H1025
RPS2H1625
RPS2H2.520
RPS2H2532
RPS2H420
RPS2H620
RPS2L1.520
RPS2L120

Catalog Number
RPS2L2.520
RPS2L420
RPS3H1.520
RPS3H1025
RPS3H1625
RPS3H2.520
RPS3H2540
RPS3H420
RPS3H625
RPS3L1.520
RPS3L120
RPS3L2.520
RPS4H1.520
RPS4H1025
RPS4H1632
RPS4H2.520
RPS4H2540
RPS4H425

Catalog Number
RPS4H625
RPS4L1.520
RPS4L120
RPS4L2.520
RPS7H1.525
RPS7H2.525
RPS7L1.525
RPS7L125
RPS7L2.525

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT